

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P314062

Luminaire Tested: **24FCZ2-55HE-UNV-L83050-CP250-W2A-U-4000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P314062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-55HE-UNV-L83050-CP250-W2A-U-4000K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.250" POLYCARB SHEET
Light Source: (336) 4000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4945.0 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 44.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P314062

CATALOG NUMBER: 24FCZ2-55HE-UNV-L83050-CP250-W2A-U-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P314062

CATALOG NUMBER: 24FCZ2-55HE-UNV-L83050-CP250-W2A-U-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	87	88	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	79	67	58	52	64	57	51	62	56	50	60	54	50	47
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	64	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	37	31	57	45	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	25	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2194	2194	2194
5°	2198	2185	2198
10°	2185	2179	2197
15°	2166	2171	2198
20°	2140	2156	2196
25°	2107	2141	2195
30°	2067	2123	2192
35°	2027	2102	2194
40°	1980	2086	2207
45°	1932	2073	2226
50°	1875	2067	2260
55°	1828	2071	2305
60°	1757	2088	2384
65°	1677	2110	2471
70°	1588	2175	2607
75°	1416	2269	2849
80°	1208	2403	2911
85°	861	2381	2787



TEST NUMBER: P314062

CATALOG NUMBER: 24FCZ2-55HE-UNV-L83050-CP250-W2A-U-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.3	3.1
10°-20°	441.3	8.9
20°-30°	666.6	13.5
30°-40°	803.4	16.2
40°-50°	843.4	17.1
50°-60°	789.0	16.0
60°-70°	651.6	13.2
70°-80°	444.0	9.0
80°-90°	151.4	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1262.2	25.5
0°-40°	2065.6	41.8
0°-60°	3698.0	74.8
0°-90°	4945.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4945.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1631	1631	1631	1631	1631	
5°	1628	1626	1618	1628	1628	154
15°	1555	1557	1559	1575	1578	438
25°	1419	1426	1442	1470	1478	653
35°	1234	1247	1280	1322	1336	771
45°	1016	1037	1089	1148	1170	783
55°	779	810	883	955	983	696
65°	527	571	663	746	776	522
75°	272	335	436	518	548	290
85°	56	110	154	174	180	70
90°	0	0	0	0	0	



TEST NUMBER: P314062

CATALOG NUMBER: 24FCZ2-55HE-UNV-L83050-CP250-W2A-U-4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1630.8	1630.8	1630.8	1630.8	1630.8
2.5°	1632.5	1630.8	1622.6	1630.8	1629.2
5°	1627.5	1625.9	1617.7	1627.5	1627.5
7.5°	1616.1	1616.1	1607.8	1619.3	1621.0
10°	1599.6	1599.6	1594.7	1607.8	1607.8
12.5°	1580.0	1580.0	1580.0	1593.1	1594.7
15°	1555.3	1557.0	1558.6	1575.0	1578.3
17.5°	1525.8	1529.1	1534.0	1553.7	1557.0
20°	1494.6	1497.9	1506.1	1529.1	1534.0
22.5°	1455.3	1463.5	1475.0	1501.2	1506.1
25°	1419.2	1425.7	1442.1	1470.0	1478.2
27.5°	1374.9	1384.7	1406.0	1435.6	1447.1
30°	1330.6	1340.4	1366.7	1401.1	1411.0
32.5°	1283.0	1297.8	1325.7	1361.7	1373.2
35°	1233.8	1246.9	1279.7	1322.4	1335.5
37.5°	1179.6	1197.7	1233.8	1279.7	1296.1
40°	1127.1	1146.8	1187.8	1237.1	1256.7
42.5°	1074.6	1094.3	1140.3	1196.0	1215.7
45°	1015.6	1036.9	1089.4	1148.5	1169.8
47.5°	956.5	982.8	1040.2	1102.5	1125.5
50°	895.8	925.3	987.7	1053.3	1079.6
52.5°	841.7	869.6	935.2	1005.7	1030.3
55°	779.3	810.5	882.7	954.9	982.8
57.5°	715.3	749.8	826.9	905.6	933.5
60°	653.0	690.7	776.0	854.8	886.0
62.5°	592.3	630.0	718.6	800.6	831.8
65°	526.7	571.0	662.8	746.5	776.0
67.5°	464.3	511.9	608.7	690.7	720.3
70°	403.6	449.5	552.9	633.3	662.8
72.5°	338.0	390.5	493.8	577.5	608.7
75°	272.3	334.7	436.4	518.4	548.0
77.5°	211.6	275.6	377.4	444.6	459.4
80°	155.9	221.5	310.1	357.7	375.7
82.5°	100.1	165.7	236.3	270.7	285.5
85°	55.8	109.9	154.2	173.9	180.5
87.5°	23.0	47.6	62.3	70.5	70.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)