

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579780

Luminaire Tested: **HC410D010-HM40525930-41MDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579780
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC410D010-HM40525930-41MDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 961.2 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579780

CATALOG NUMBER: HC410D010-HM40525930-41MDC

Luminous Intensity Polar Plot





TEST NUMBER: P579780

CATALOG NUMBER: HC410D010-HM40525930-41MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86		
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80		
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74		
5	91	83	77	72	90	82	76	72	80	75	72	78	74	71	77	73	70	69		
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64		
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60		
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	64	60	57	56		
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52		
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	111319
5°	113367
10°	116882
15°	115578
20°	106125
25°	91566
30°	74603
35°	55247
40°	31704
45°	15333
50°	7292
55°	2538
60°	937
65°	525
70°	469
75°	286
80°	0
85°	0



TEST NUMBER: P579780

CATALOG NUMBER: HC410D010-HM40525930-41MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.1	9.2
10°-20°	250.9	26.1
20°-30°	306.4	31.9
30°-40°	225.3	23.4
40°-50°	74.7	7.8
50°-60°	13.2	1.4
60°-70°	2.0	0.2
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	645.4	67.1
0°-40°	870.7	90.6
0°-60°	958.5	99.7
0°-90°	961.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	961.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	902	
5°	916	88
15°	905	251
25°	673	306
35°	367	225
45°	88	75
55°	12	13
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P579780

CATALOG NUMBER: HC410D010-HM40525930-41MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	902.5
2.5°	903.2
5°	915.6
7.5°	929.4
10°	933.2
12.5°	924.4
15°	905.1
17.5°	865.2
20°	808.5
22.5°	742.5
25°	672.8
27.5°	599.8
30°	523.8
32.5°	447.9
35°	366.9
37.5°	284.6
40°	196.9
42.5°	130.2
45°	87.9
47.5°	58.6
50°	38.0
52.5°	22.4
55°	11.8
57.5°	5.0
60°	3.8
62.5°	2.5
65°	1.8
67.5°	1.3
70°	1.3
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)