

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579802

Luminaire Tested: **HC410D010-HM40525935-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579802
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC410D010-HM40525935-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 902.3 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579802

CATALOG NUMBER: HC410D010-HM40525935-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P579802

CATALOG NUMBER: HC410D010-HM40525935-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79262
5°	78686
10°	76627
15°	74600
20°	71262
25°	66402
30°	58466
35°	46107
40°	33475
45°	24596
50°	19995
55°	16795
60°	15221
65°	13980
70°	13019
75°	11867
80°	10726
85°	9341



TEST NUMBER: P579802

CATALOG NUMBER: HC410D010-HM40525935-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.9	6.6
10°-20°	163.9	18.2
20°-30°	222.2	24.6
30°-40°	190.6	21.1
40°-50°	112.5	12.5
50°-60°	71.3	7.9
60°-70°	48.0	5.3
70°-80°	26.5	2.9
80°-90°	7.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	445.9	49.4
0°-40°	636.6	70.6
0°-60°	820.5	90.9
0°-90°	902.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	902.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	643	
5°	636	60
15°	584	164
25°	488	222
35°	306	191
45°	141	113
55°	78	71
65°	48	48
75°	25	26
85°	7	7
90°	0	



TEST NUMBER: P579802

CATALOG NUMBER: HC410D010-HM40525935-41NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	642.6
2.5°	638.1
5°	635.5
7.5°	626.9
10°	611.8
12.5°	598.7
15°	584.2
17.5°	565.9
20°	542.9
22.5°	517.4
25°	487.9
27.5°	453.2
30°	410.5
32.5°	360.1
35°	306.2
37.5°	254.5
40°	207.9
42.5°	169.2
45°	141.0
47.5°	120.6
50°	104.2
52.5°	90.5
55°	78.1
57.5°	68.2
60°	61.7
62.5°	55.1
65°	47.9
67.5°	42.0
70°	36.1
72.5°	30.2
75°	24.9
77.5°	19.7
80°	15.1
82.5°	10.5
85°	6.6
87.5°	2.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)