

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P314092

Luminaire Tested: **24FCZ2-65HE-UNV-L83050-CA08-W2A-U-4000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P314092
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-65HE-UNV-L83050-CA08-W2A-U-4000K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.08" ACRYLIC SHEET
Light Source: (336) 4000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6275.0 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 53.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P314092

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-CA08-W2A-U-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P314092

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-CA08-W2A-U-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	87	88	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	79	67	58	52	64	57	51	62	56	50	60	54	50	47
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	64	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	37	31	57	45	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	25	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2784	2784	2784
5°	2789	2773	2789
10°	2773	2765	2788
15°	2749	2755	2790
20°	2716	2737	2787
25°	2674	2717	2785
30°	2623	2694	2782
35°	2572	2667	2784
40°	2512	2647	2801
45°	2452	2630	2825
50°	2379	2623	2867
55°	2320	2628	2925
60°	2230	2650	3025
65°	2128	2678	3135
70°	2015	2760	3309
75°	1797	2879	3615
80°	1533	3049	3694
85°	1093	3021	3535



TEST NUMBER: P314092

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-CA08-W2A-U-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.8	3.1
10°-20°	560.0	8.9
20°-30°	845.8	13.5
30°-40°	1019.4	16.2
40°-50°	1070.2	17.1
50°-60°	1001.2	16.0
60°-70°	826.9	13.2
70°-80°	563.4	9.0
80°-90°	192.2	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1601.7	25.5
0°-40°	2621.1	41.8
0°-60°	4692.6	74.8
0°-90°	6275.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6275.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2069	2069	2069	2069	2069	
5°	2065	2063	2053	2065	2065	196
15°	1974	1976	1978	1999	2003	556
25°	1801	1809	1830	1865	1876	829
35°	1566	1582	1624	1678	1695	978
45°	1289	1316	1382	1457	1484	994
55°	989	1028	1120	1212	1247	883
65°	668	724	841	947	985	663
75°	346	425	554	658	695	369
85°	71	140	196	221	229	89
90°	0	0	0	0	0	



TEST NUMBER: P314092

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-CA08-W2A-U-4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2069.4	2069.4	2069.4	2069.4	2069.4
2.5°	2071.5	2069.4	2059.0	2069.4	2067.4
5°	2065.3	2063.2	2052.8	2065.3	2065.3
7.5°	2050.7	2050.7	2040.3	2054.9	2056.9
10°	2029.9	2029.9	2023.6	2040.3	2040.3
12.5°	2004.9	2004.9	2004.9	2021.6	2023.6
15°	1973.7	1975.8	1977.8	1998.7	2002.8
17.5°	1936.2	1940.4	1946.6	1971.6	1975.8
20°	1896.6	1900.8	1911.2	1940.4	1946.6
22.5°	1846.7	1857.1	1871.7	1905.0	1911.2
25°	1800.9	1809.2	1830.0	1865.4	1875.8
27.5°	1744.7	1757.2	1784.2	1821.7	1836.3
30°	1688.4	1700.9	1734.2	1778.0	1790.5
32.5°	1628.1	1646.8	1682.2	1728.0	1742.6
35°	1565.6	1582.3	1623.9	1678.0	1694.7
37.5°	1496.9	1519.8	1565.6	1623.9	1644.7
40°	1430.3	1455.3	1507.3	1569.8	1594.8
42.5°	1363.7	1388.6	1446.9	1517.7	1542.7
45°	1288.7	1315.8	1382.4	1457.4	1484.4
47.5°	1213.8	1247.1	1319.9	1399.1	1428.2
50°	1136.7	1174.2	1253.3	1336.6	1369.9
52.5°	1068.0	1103.4	1186.7	1276.2	1307.5
55°	988.9	1028.5	1120.1	1211.7	1247.1
57.5°	907.7	951.4	1049.3	1149.2	1184.6
60°	828.6	876.5	984.8	1084.7	1124.2
62.5°	751.6	799.5	911.9	1016.0	1055.5
65°	668.3	724.5	841.1	947.3	984.8
67.5°	589.2	649.6	772.4	876.5	914.0
70°	512.2	570.4	701.6	803.6	841.1
72.5°	428.9	495.5	626.7	732.8	772.4
75°	345.6	424.7	553.8	657.9	695.4
77.5°	268.6	349.8	478.8	564.2	582.9
80°	197.8	281.1	393.5	453.9	476.8
82.5°	127.0	210.3	299.8	343.5	362.3
85°	70.8	139.5	195.7	220.7	229.0
87.5°	29.1	60.4	79.1	89.5	89.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)