

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579835

Luminaire Tested: **HC415D010-HM40525827-41NDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579835  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC415D010-HM40525827-41NDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1316.0 lumens  
Efficiency: N/A  
Efficacy: 94.0 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579835

CATALOG NUMBER: HC415D010-HM40525827-41NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P579835

CATALOG NUMBER: HC415D010-HM40525827-41NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87			87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			81
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			71
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51			51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	193825
5°	193588
10°	189814
15°	176490
20°	151791
25°	121943
30°	95198
35°	66645
40°	34200
45°	17374
50°	8712
55°	3247
60°	1307
65°	1022
70°	649
75°	429
80°	639
85°	0



TEST NUMBER: P579835

CATALOG NUMBER: HC415D010-HM40525827-41NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.8	11.2
10°-20°	381.5	29.0
20°-30°	411.0	31.2
30°-40°	270.0	20.5
40°-50°	84.0	6.4
50°-60°	16.5	1.3
60°-70°	3.5	0.3
70°-80°	1.3	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	940.4	71.5
0°-40°	1210.4	92.0
0°-60°	1310.9	99.6
0°-90°	1316.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1316.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1571	
5°	1564	148
15°	1382	382
25°	896	411
35°	443	270
45°	100	84
55°	15	16
65°	4	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P579835

CATALOG NUMBER: HC415D010-HM40525827-41NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1571.4
2.5°	1563.5
5°	1563.5
7.5°	1551.1
10°	1515.5
12.5°	1458.7
15°	1382.1
17.5°	1279.9
20°	1156.4
22.5°	1023.1
25°	896.0
27.5°	777.7
30°	668.4
32.5°	565.3
35°	442.6
37.5°	308.5
40°	212.4
42.5°	146.7
45°	99.6
47.5°	67.5
50°	45.4
52.5°	28.4
55°	15.1
57.5°	6.3
60°	5.3
62.5°	4.4
65°	3.5
67.5°	2.6
70°	1.8
72.5°	1.8
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)