

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579837

Luminaire Tested: **HC415D010-HM40525827-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579837
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC415D010-HM40525827-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1283.9 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579837

CATALOG NUMBER: HC415D010-HM40525827-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P579837

CATALOG NUMBER: HC415D010-HM40525827-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108853
5°	108290
10°	106311
15°	104060
20°	99601
25°	92628
30°	81995
35°	64703
40°	48418
45°	37242
50°	30223
55°	25053
60°	22153
65°	20518
70°	18934
75°	17395
80°	15840
85°	12596



TEST NUMBER: P579837

CATALOG NUMBER: HC415D010-HM40525827-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.7	6.4
10°-20°	228.5	17.8
20°-30°	310.3	24.2
30°-40°	268.8	20.9
40°-50°	168.8	13.1
50°-60°	106.1	8.3
60°-70°	69.7	5.4
70°-80°	38.4	3.0
80°-90°	10.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	621.5	48.4
0°-40°	890.3	69.3
0°-60°	1165.2	90.8
0°-90°	1283.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1283.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	882	
5°	875	83
15°	815	229
25°	681	310
35°	430	269
45°	214	169
55°	116	106
65°	70	70
75°	36	38
85°	9	11
90°	0	



TEST NUMBER: P579837

CATALOG NUMBER: HC415D010-HM40525827-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	882.5
2.5°	877.2
5°	874.6
7.5°	865.6
10°	848.8
12.5°	831.8
15°	814.9
17.5°	791.8
20°	758.8
22.5°	721.5
25°	680.6
27.5°	633.4
30°	575.7
32.5°	505.3
35°	429.7
37.5°	360.3
40°	300.7
42.5°	253.6
45°	213.5
47.5°	183.3
50°	157.5
52.5°	135.2
55°	116.5
57.5°	100.5
60°	89.8
62.5°	80.0
65°	70.3
67.5°	60.5
70°	52.5
72.5°	43.5
75°	36.5
77.5°	28.4
80°	22.3
82.5°	15.1
85°	8.9
87.5°	3.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)