

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579857

Luminaire Tested: **HC415D010-HM40525830-41PSMDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579857  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC415D010-HM40525830-41PSMDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1361.8 lumens  
Efficiency: N/A  
Efficacy: 97.3 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579857

CATALOG NUMBER: HC415D010-HM40525830-41PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P579857

CATALOG NUMBER: HC415D010-HM40525830-41PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78			
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70			
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63			
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	118276
5°	117552
10°	115053
15°	112514
20°	107306
25°	99323
30°	86396
35°	65245
40°	47290
45°	36946
50°	31585
55°	27332
60°	25187
65°	23028
70°	21530
75°	19730
80°	18468
85°	17690



TEST NUMBER: P579857

CATALOG NUMBER: HC415D010-HM40525830-41PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.7	6.6
10°-20°	246.8	18.1
20°-30°	331.8	24.4
30°-40°	272.9	20.0
40°-50°	167.6	12.3
50°-60°	116.0	8.5
60°-70°	79.1	5.8
70°-80°	44.0	3.2
80°-90°	14.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	668.3	49.1
0°-40°	941.2	69.1
0°-60°	1224.7	89.9
0°-90°	1361.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1361.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	959	
5°	949	90
15°	881	247
25°	730	332
35°	433	273
45°	212	168
55°	127	116
65°	79	79
75°	41	44
85°	12	14
90°	0	



TEST NUMBER: P579857

CATALOG NUMBER: HC415D010-HM40525830-41PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	958.9
2.5°	952.2
5°	949.4
7.5°	938.8
10°	918.6
12.5°	900.3
15°	881.1
17.5°	853.1
20°	817.5
22.5°	775.1
25°	729.8
27.5°	674.9
30°	606.6
32.5°	522.8
35°	433.3
37.5°	356.2
40°	293.7
42.5°	245.5
45°	211.8
47.5°	185.8
50°	164.6
52.5°	145.4
55°	127.1
57.5°	113.6
60°	102.1
62.5°	90.5
65°	78.9
67.5°	69.4
70°	59.7
72.5°	50.0
75°	41.4
77.5°	32.7
80°	26.0
82.5°	19.2
85°	12.5
87.5°	6.7
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)