

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P314236

Luminaire Tested: **24FCZ2-35HE-UNV-L83050-S-CP250-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P314236  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-35HE-UNV-L83050-S-CP250-W2A-U-3500K  
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.250" POLYCARB SHEET  
Light Source: (336) 3500K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3137.0 lumens  
Efficiency: N/A  
Efficacy: 120.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 26  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P314236

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-S-CP250-W2A-U-3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P314236

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-S-CP250-W2A-U-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1483	1483	1483
5°	1482	1478	1487
10°	1476	1476	1487
15°	1461	1468	1484
20°	1442	1457	1480
25°	1416	1442	1470
30°	1384	1426	1458
35°	1353	1403	1447
40°	1307	1379	1430
45°	1265	1352	1414
50°	1216	1326	1397
55°	1162	1302	1384
60°	1107	1282	1381
65°	1037	1259	1389
70°	960	1266	1427
75°	860	1290	1508
80°	695	1367	1475
85°	523	1200	1169



TEST NUMBER: P314236

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-S-CP250-W2A-U-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.3	3.3
10°-20°	298.1	9.5
20°-30°	448.1	14.3
30°-40°	533.8	17.0
40°-50°	546.3	17.4
50°-60°	491.8	15.7
60°-70°	386.2	12.3
70°-80°	250.7	8.0
80°-90°	77.5	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	850.6	27.1
0°-40°	1384.4	44.1
0°-60°	2422.5	77.2
0°-90°	3137.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3137.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1102	1102	1102	1102	1102	
5°	1097	1099	1094	1100	1101	104
15°	1049	1052	1054	1063	1065	296
25°	954	962	972	988	990	439
35°	824	834	854	875	881	514
45°	665	681	710	737	743	512
55°	495	517	555	584	590	444
65°	326	351	396	428	436	324
75°	165	197	248	282	290	175
85°	34	63	78	76	76	41
90°	0	0	0	0	0	



TEST NUMBER: P314236

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-S-CP250-W2A-U-3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1102.0	1102.0	1102.0	1102.0	1102.0
2.5°	1103.0	1103.0	1098.1	1103.0	1104.0
5°	1097.1	1099.1	1094.1	1100.1	1101.1
7.5°	1091.1	1091.1	1088.1	1094.1	1095.1
10°	1080.1	1081.1	1080.1	1087.1	1088.1
12.5°	1066.2	1068.2	1069.2	1076.1	1077.1
15°	1049.2	1052.2	1054.2	1063.2	1065.2
17.5°	1030.3	1033.3	1038.3	1048.2	1050.2
20°	1007.4	1011.4	1017.4	1030.3	1033.3
22.5°	982.5	986.5	996.4	1008.4	1013.4
25°	953.6	961.6	971.5	987.5	990.4
27.5°	924.7	931.7	944.6	961.6	965.5
30°	890.8	901.8	917.7	934.6	938.6
32.5°	857.9	868.9	887.8	905.8	910.7
35°	824.0	834.0	853.9	874.9	880.8
37.5°	785.2	798.1	820.1	841.0	847.0
40°	744.3	760.3	785.2	807.1	814.1
42.5°	705.5	722.4	747.3	771.2	779.2
45°	664.6	680.6	710.5	737.4	743.3
47.5°	622.8	640.7	672.6	699.5	709.5
50°	580.9	599.8	633.7	661.6	667.6
52.5°	539.1	559.0	594.9	624.8	627.7
55°	495.2	517.1	555.0	583.9	589.9
57.5°	455.4	474.3	515.2	545.0	552.0
60°	411.5	432.4	476.3	504.2	513.2
62.5°	369.7	391.6	437.4	465.3	473.3
65°	325.8	350.7	395.6	428.5	436.4
67.5°	288.0	311.9	359.7	391.6	399.6
70°	244.1	271.0	321.8	354.7	362.7
72.5°	206.3	234.2	285.0	316.9	328.8
75°	165.4	197.3	248.1	282.0	290.0
77.5°	125.5	162.4	214.2	240.1	240.1
80°	89.7	128.5	176.4	188.3	190.3
82.5°	58.8	96.7	130.5	129.5	129.5
85°	33.9	62.8	77.7	75.7	75.7
87.5°	13.0	25.9	27.9	27.9	26.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)