

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P314301

Luminaire Tested: **24FCZ2-40-UNV-L83050-S-CP125-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P314301
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-40-UNV-L83050-S-CP125-W2A-U-3500K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.125" POLYCARB SHEET
Light Source: (168) 3500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3799.0 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 32.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P314301

CATALOG NUMBER: 24FCZ2-40-UNV-L83050-S-CP125-W2A-U-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P314301

CATALOG NUMBER: 24FCZ2-40-UNV-L83050-S-CP125-W2A-U-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1796	1796	1796
5°	1794	1790	1801
10°	1787	1787	1800
15°	1770	1778	1797
20°	1747	1764	1792
25°	1714	1747	1781
30°	1676	1727	1766
35°	1639	1699	1752
40°	1583	1670	1732
45°	1532	1637	1713
50°	1473	1607	1692
55°	1407	1577	1676
60°	1341	1552	1672
65°	1256	1525	1683
70°	1163	1533	1728
75°	1041	1562	1826
80°	841	1655	1786
85°	633	1453	1416



TEST NUMBER: P314301

CATALOG NUMBER: 24FCZ2-40-UNV-L83050-S-CP125-W2A-U-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	3.3
10°-20°	361.0	9.5
20°-30°	542.7	14.3
30°-40°	646.4	17.0
40°-50°	661.6	17.4
50°-60°	595.6	15.7
60°-70°	467.8	12.3
70°-80°	303.6	8.0
80°-90°	93.9	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1030.1	27.1
0°-40°	1676.5	44.1
0°-60°	2933.8	77.2
0°-90°	3799.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3799.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1335	1335	1335	1335	1335	
5°	1329	1331	1325	1332	1333	126
15°	1271	1274	1277	1288	1290	358
25°	1155	1164	1176	1196	1200	532
35°	998	1010	1034	1060	1067	623
45°	805	824	860	893	900	621
55°	600	626	672	707	714	538
65°	395	425	479	519	528	393
75°	200	239	300	342	351	212
85°	41	76	94	92	92	50
90°	0	0	0	0	0	



TEST NUMBER: P314301

CATALOG NUMBER: 24FCZ2-40-UNV-L83050-S-CP125-W2A-U-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1335.8	1335.8	1329.8	1335.8	1337.0
5°	1328.6	1331.0	1325.0	1332.2	1333.4
7.5°	1321.3	1321.3	1317.7	1325.0	1326.2
10°	1308.1	1309.3	1308.1	1316.5	1317.7
12.5°	1291.2	1293.6	1294.8	1303.2	1304.4
15°	1270.7	1274.3	1276.7	1287.6	1290.0
17.5°	1247.7	1251.4	1257.4	1269.5	1271.9
20°	1220.0	1224.8	1232.0	1247.7	1251.4
22.5°	1189.8	1194.6	1206.7	1221.2	1227.2
25°	1154.8	1164.5	1176.5	1195.8	1199.5
27.5°	1119.8	1128.3	1144.0	1164.5	1169.3
30°	1078.8	1092.1	1111.4	1131.9	1136.7
32.5°	1039.0	1052.2	1075.2	1096.9	1102.9
35°	997.9	1010.0	1034.1	1059.5	1066.7
37.5°	950.9	966.6	993.1	1018.5	1025.7
40°	901.4	920.7	950.9	977.4	985.9
42.5°	854.3	874.9	905.0	934.0	943.6
45°	804.9	824.2	860.4	893.0	900.2
47.5°	754.2	775.9	814.5	847.1	859.2
50°	703.5	726.4	767.5	801.3	808.5
52.5°	652.8	677.0	720.4	756.6	760.2
55°	599.7	626.3	672.1	707.1	714.4
57.5°	551.5	574.4	623.9	660.1	668.5
60°	498.4	523.7	576.8	610.6	621.5
62.5°	447.7	474.2	529.7	563.5	573.2
65°	394.6	424.8	479.1	518.9	528.5
67.5°	348.7	377.7	435.6	474.2	483.9
70°	295.6	328.2	389.8	429.6	439.2
72.5°	249.8	283.6	345.1	383.7	398.2
75°	200.3	238.9	300.5	341.5	351.2
77.5°	152.0	196.7	259.4	290.8	290.8
80°	108.6	155.7	213.6	228.1	230.5
82.5°	71.2	117.1	158.1	156.9	156.9
85°	41.0	76.0	94.1	91.7	91.7
87.5°	15.7	31.4	33.8	33.8	32.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)