

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579922

Luminaire Tested: **HC415D010-HM40525930-41WDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579922  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC415D010-HM40525930-41WDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1351.6 lumens  
Efficiency: N/A  
Efficacy: 96.5 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579922

CATALOG NUMBER: HC415D010-HM40525930-41WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P579922

CATALOG NUMBER: HC415D010-HM40525930-41WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	113638
5°	114493
10°	115930
15°	118835
20°	119711
25°	116295
30°	106621
35°	87726
40°	63956
45°	41516
50°	23411
55°	11096
60°	4366
65°	2714
70°	1839
75°	1191
80°	568
85°	1132



TEST NUMBER: P579922

CATALOG NUMBER: HC415D010-HM40525930-41WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.3	6.5
10°-20°	262.4	19.4
20°-30°	389.1	28.8
30°-40°	359.4	26.6
40°-50°	187.7	13.9
50°-60°	51.4	3.8
60°-70°	9.9	0.7
70°-80°	2.8	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	739.8	54.7
0°-40°	1099.3	81.3
0°-60°	1338.4	99.0
0°-90°	1351.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1351.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	921	
5°	925	88
15°	931	262
25°	854	389
35°	583	359
45°	238	188
55°	52	51
65°	9	10
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P579922

CATALOG NUMBER: HC415D010-HM40525930-41WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	921.3
2.5°	918.8
5°	924.7
7.5°	927.3
10°	925.6
12.5°	927.3
15°	930.6
17.5°	927.3
20°	912.0
22.5°	887.4
25°	854.5
27.5°	809.5
30°	748.6
32.5°	671.5
35°	582.6
37.5°	489.5
40°	397.2
42.5°	312.4
45°	238.0
47.5°	174.4
50°	122.0
52.5°	81.3
55°	51.6
57.5°	30.5
60°	17.7
62.5°	12.7
65°	9.3
67.5°	6.8
70°	5.1
72.5°	3.4
75°	2.5
77.5°	1.7
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)