

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579938

Luminaire Tested: **HC4R15D010-HM40525935-42RMDC**

Issue Date: 9/23/2021

Test Information

Test Method: LM-41-14
Report Number: P579938
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/23/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC4R15D010-HM40525935-42RMDC
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1382.9 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579938

CATALOG NUMBER: HC4R15D010-HM40525935-42RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P579938

CATALOG NUMBER: HC4R15D010-HM40525935-42RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	156698
5°	160058
10°	166380
15°	166453
20°	153891
25°	132980
30°	108188
35°	79475
40°	45938
45°	21456
50°	9921
55°	3441
60°	1085
65°	788
70°	649
75°	429
80°	0
85°	0



TEST NUMBER: P579938

CATALOG NUMBER: HC4R15D010-HM40525935-42RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.7	9.0
10°-20°	361.2	26.1
20°-30°	444.9	32.2
30°-40°	324.8	23.5
40°-50°	105.9	7.7
50°-60°	17.7	1.3
60°-70°	2.7	0.2
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	930.8	67.3
0°-40°	1255.6	90.8
0°-60°	1379.2	99.7
0°-90°	1382.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1382.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1270	
5°	1293	125
15°	1304	361
25°	977	445
35°	528	325
45°	123	106
55°	16	18
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P579938

CATALOG NUMBER: HC4R15D010-HM40525935-42RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	1270.4
2.5°	1271.3
5°	1292.7
7.5°	1317.7
10°	1328.4
12.5°	1324.8
15°	1303.5
17.5°	1249.9
20°	1172.4
22.5°	1078.8
25°	977.1
27.5°	871.1
30°	759.6
32.5°	645.5
35°	527.8
37.5°	409.2
40°	285.3
42.5°	186.4
45°	123.0
47.5°	81.2
50°	51.7
52.5°	30.4
55°	16.0
57.5°	6.3
60°	4.4
62.5°	3.5
65°	2.7
67.5°	1.8
70°	1.8
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)