

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592647

Luminaire Tested: **HC415D010-HM40525950-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592647
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC415D010-HM40525950-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1334.0 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592647

CATALOG NUMBER: HC415D010-HM40525950-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P592647

CATALOG NUMBER: HC415D010-HM40525950-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113096
5°	112500
10°	110432
15°	108108
20°	103487
25°	96234
30°	85186
35°	67218
40°	50301
45°	38690
50°	31393
55°	26042
60°	23016
65°	21306
70°	19691
75°	18062
80°	16408
85°	13020



TEST NUMBER: P592647

CATALOG NUMBER: HC415D010-HM40525950-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.9	6.4
10°-20°	237.4	17.8
20°-30°	322.4	24.2
30°-40°	279.3	20.9
40°-50°	175.3	13.1
50°-60°	110.3	8.3
60°-70°	72.5	5.4
70°-80°	40.0	3.0
80°-90°	10.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	645.7	48.4
0°-40°	925.0	69.3
0°-60°	1210.6	90.7
0°-90°	1334.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1334.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	917	
5°	909	86
15°	847	237
25°	707	322
35°	446	279
45°	222	175
55°	121	110
65°	73	72
75°	38	40
85°	9	11
90°	0	



TEST NUMBER: P592647

CATALOG NUMBER: HC415D010-HM40525950-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	916.9
2.5°	911.3
5°	908.6
7.5°	899.4
10°	881.7
12.5°	864.2
15°	846.6
17.5°	822.6
20°	788.4
22.5°	749.6
25°	707.1
27.5°	658.1
30°	598.1
32.5°	525.0
35°	446.4
37.5°	374.3
40°	312.4
42.5°	263.4
45°	221.8
47.5°	190.4
50°	163.6
52.5°	140.5
55°	121.1
57.5°	104.5
60°	93.3
62.5°	83.2
65°	73.0
67.5°	62.9
70°	54.6
72.5°	45.3
75°	37.9
77.5°	29.6
80°	23.1
82.5°	15.7
85°	9.2
87.5°	3.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)