

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P314467

Luminaire Tested: **24FCZ2-65HE-UNV-L83050-S-CA08-W2A-U-4000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P314467  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-65HE-UNV-L83050-S-CA08-W2A-U-4000K  
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.08" ACRYLIC SHEET  
Light Source: (336) 4000K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6593.0 lumens  
Efficiency: N/A  
Efficacy: 122.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 53.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P314467

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-S-CA08-W2A-U-4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P314467

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-S-CA08-W2A-U-4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3116	3116	3116
5°	3114	3106	3125
10°	3102	3102	3124
15°	3072	3086	3118
20°	3031	3062	3110
25°	2975	3031	3090
30°	2909	2997	3065
35°	2845	2948	3041
40°	2748	2898	3005
45°	2658	2841	2973
50°	2556	2788	2937
55°	2441	2736	2908
60°	2327	2694	2902
65°	2180	2647	2920
70°	2019	2661	2999
75°	1807	2711	3168
80°	1461	2872	3099
85°	1099	2521	2458



TEST NUMBER: P314467

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-S-CA08-W2A-U-4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	219.3	3.3
10°-20°	626.5	9.5
20°-30°	941.8	14.3
30°-40°	1121.9	17.0
40°-50°	1148.2	17.4
50°-60°	1033.7	15.7
60°-70°	811.8	12.3
70°-80°	526.9	8.0
80°-90°	162.9	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1787.6	27.1
0°-40°	2909.5	44.1
0°-60°	5091.4	77.2
0°-90°	6593.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6593.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2316	2316	2316	2316	2316	
5°	2306	2310	2299	2312	2314	219
15°	2205	2212	2216	2234	2239	622
25°	2004	2021	2042	2075	2082	923
35°	1732	1753	1795	1839	1851	1080
45°	1397	1430	1493	1550	1562	1077
55°	1041	1087	1166	1227	1240	933
65°	685	737	831	900	917	682
75°	348	415	522	593	609	368
85°	71	132	163	159	159	86
90°	0	0	0	0	0	



TEST NUMBER: P314467

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-S-CA08-W2A-U-4000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2316.2	2316.2	2316.2	2316.2	2316.2
2.5°	2318.3	2318.3	2307.8	2318.3	2320.4
5°	2305.7	2309.9	2299.4	2312.0	2314.1
7.5°	2293.1	2293.1	2286.8	2299.4	2301.5
10°	2270.1	2272.2	2270.1	2284.8	2286.8
12.5°	2240.8	2245.0	2247.1	2261.7	2263.8
15°	2205.2	2211.5	2215.6	2234.5	2238.7
17.5°	2165.4	2171.7	2182.1	2203.1	2207.3
20°	2117.2	2125.6	2138.2	2165.4	2171.7
22.5°	2064.9	2073.2	2094.2	2119.3	2129.8
25°	2004.1	2020.9	2041.8	2075.3	2081.6
27.5°	1943.4	1958.1	1985.3	2020.9	2029.3
30°	1872.2	1895.2	1928.7	1964.3	1972.7
32.5°	1803.1	1826.1	1865.9	1903.6	1914.1
35°	1731.9	1752.8	1794.7	1838.7	1851.3
37.5°	1650.2	1677.4	1723.5	1767.5	1780.1
40°	1564.4	1597.9	1650.2	1696.3	1710.9
42.5°	1482.7	1518.3	1570.6	1620.9	1637.6
45°	1396.8	1430.3	1493.2	1549.7	1562.3
47.5°	1308.9	1346.6	1413.6	1470.1	1491.1
50°	1220.9	1260.7	1331.9	1390.5	1403.1
52.5°	1133.0	1174.8	1250.2	1313.1	1319.3
55°	1040.8	1086.9	1166.5	1227.2	1239.8
57.5°	957.0	996.8	1082.7	1145.5	1160.2
60°	864.9	908.9	1001.0	1059.7	1078.5
62.5°	776.9	823.0	919.3	978.0	994.7
65°	684.8	737.2	831.4	900.5	917.3
67.5°	605.2	655.5	756.0	823.0	839.8
70°	513.1	569.6	676.4	745.5	762.3
72.5°	433.5	492.1	598.9	665.9	691.1
75°	347.6	414.6	521.5	592.7	609.4
77.5°	263.9	341.4	450.2	504.7	504.7
80°	188.5	270.1	370.7	395.8	400.0
82.5°	123.6	203.1	274.3	272.2	272.2
85°	71.2	131.9	163.3	159.2	159.2
87.5°	27.2	54.4	58.6	58.6	56.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)