

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592661

Luminaire Tested: **HC4R20D010-HM40525850-42RMDC**

Issue Date: 9/23/2021

Test Information

Test Method: LM-41-14
Report Number: P592661
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/23/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC4R20D010-HM40525850-42RMDC
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2164.1 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592661

CATALOG NUMBER: HC4R20D010-HM40525850-42RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P592661

CATALOG NUMBER: HC4R20D010-HM40525850-42RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	245236
5°	250494
10°	260379
15°	260476
20°	240826
25°	208119
30°	169318
35°	124377
40°	71894
45°	33597
50°	15543
55°	5398
60°	1727
65°	1197
70°	1010
75°	667
80°	0
85°	0



TEST NUMBER: P592661

CATALOG NUMBER: HC4R20D010-HM40525850-42RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.2	9.0
10°-20°	565.3	26.1
20°-30°	696.2	32.2
30°-40°	508.3	23.5
40°-50°	165.7	7.7
50°-60°	27.7	1.3
60°-70°	4.3	0.2
70°-80°	1.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1456.7	67.3
0°-40°	1965.0	90.8
0°-60°	2158.4	99.7
0°-90°	2164.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2164.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1988	
5°	2023	195
15°	2040	565
25°	1529	696
35°	826	508
45°	193	166
55°	25	28
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P592661

CATALOG NUMBER: HC4R20D010-HM40525850-42RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	1988.2
2.5°	1989.6
5°	2023.1
7.5°	2062.2
10°	2078.9
12.5°	2073.3
15°	2039.8
17.5°	1956.1
20°	1834.7
22.5°	1688.3
25°	1529.2
27.5°	1363.1
30°	1188.8
32.5°	1010.2
35°	826.0
37.5°	640.4
40°	446.5
42.5°	291.6
45°	192.6
47.5°	127.0
50°	81.0
52.5°	47.5
55°	25.1
57.5°	9.7
60°	7.0
62.5°	5.6
65°	4.1
67.5°	2.8
70°	2.8
72.5°	1.4
75°	1.4
77.5°	1.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)