

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P256315

Luminaire Tested: **HC4R40D010-HM434840-42RMDC**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P256315  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1805-779-41)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC4R40D010-HM434840-42RMDC  
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3834.7 lumens  
Efficiency: N/A  
Efficacy: 95.9 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.03  
Luminous Opening: Circular (Dia: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 40  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P256315  
CATALOG NUMBER: HC4R40D010-HM434840-42RMDC

### Luminous Intensity Polar Plot





TEST NUMBER: P256315

CATALOG NUMBER: HC4R40D010-HM434840-42RMDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		88	84	81		85	82	80	78
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	63	61
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58	53	50	49
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55	50	47	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	285884
5°	287983
10°	292847
15°	301709
20°	308525
25°	297082
30°	253260
35°	182804
40°	118470
45°	73448
50°	29020
55°	10552
60°	6042
65°	3574
70°	2935
75°	1958
80°	0
85°	0



TEST NUMBER: P256315

CATALOG NUMBER: HC4R40D010-HM434840-42RMDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	281.3	7.3
10°-20°	845.6	22.1
20°-30°	1242.7	32.4
30°-40°	962.2	25.1
40°-50°	408.3	10.6
50°-60°	71.2	1.9
60°-70°	17.8	0.5
70°-80°	5.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2369.7	61.8
0°-40°	3331.8	86.9
0°-60°	3811.4	99.4
0°-90°	3834.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3834.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2933	
5°	2944	281
15°	2990	846
25°	2763	1243
35°	1536	962
45°	533	408
55°	62	71
65°	16	18
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P256315

CATALOG NUMBER: HC4R40D010-HM434840-42RMDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2933.4
2.5°	2933.4
5°	2943.7
7.5°	2948.9
10°	2959.2
12.5°	2974.8
15°	2990.3
17.5°	2995.5
20°	2974.8
22.5°	2902.3
25°	2762.7
27.5°	2545.4
30°	2250.5
32.5°	1898.7
35°	1536.5
37.5°	1205.4
40°	931.2
42.5°	713.9
45°	532.9
47.5°	341.5
50°	191.4
52.5°	108.6
55°	62.1
57.5°	41.4
60°	31.0
62.5°	20.7
65°	15.5
67.5°	15.5
70°	10.3
72.5°	5.2
75°	5.2
77.5°	5.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)