

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579703

Luminaire Tested: **HC410D010-HM40525830-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579703
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC410D010-HM40525830-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1143.3 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579703

CATALOG NUMBER: HC410D010-HM40525830-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P579703

CATALOG NUMBER: HC410D010-HM40525830-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 |
| 1 | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 100 | 102 | 99 | 97 | 98 | 96 | 94 | 94 | 93 | 92 | 90 | | | 90 |
| 2 | 104 | 98 | 93 | 89 | 102 | 96 | 92 | 88 | 93 | 89 | 86 | 90 | 87 | 84 | 87 | 84 | 82 | 80 | | | 80 |
| 3 | 98 | 89 | 83 | 78 | 95 | 88 | 82 | 78 | 85 | 80 | 76 | 83 | 78 | 75 | 80 | 77 | 74 | 72 | | | 72 |
| 4 | 91 | 82 | 75 | 70 | 89 | 81 | 74 | 69 | 78 | 73 | 69 | 76 | 72 | 68 | 74 | 70 | 67 | 65 | | | 65 |
| 5 | 86 | 75 | 68 | 63 | 84 | 74 | 68 | 63 | 72 | 67 | 62 | 71 | 65 | 61 | 69 | 64 | 61 | 59 | | | 59 |
| 6 | 80 | 70 | 62 | 57 | 79 | 69 | 62 | 57 | 67 | 61 | 57 | 66 | 60 | 56 | 64 | 59 | 56 | 54 | | | 54 |
| 7 | 76 | 64 | 57 | 52 | 74 | 64 | 57 | 52 | 62 | 56 | 52 | 61 | 56 | 51 | 60 | 55 | 51 | 49 | | | 49 |
| 8 | 71 | 60 | 53 | 48 | 70 | 59 | 53 | 48 | 58 | 52 | 48 | 57 | 51 | 47 | 56 | 51 | 47 | 46 | | | 46 |
| 9 | 67 | 56 | 49 | 44 | 66 | 55 | 49 | 44 | 54 | 48 | 44 | 53 | 48 | 44 | 52 | 47 | 44 | 42 | | | 42 |
| 10 | 64 | 52 | 46 | 41 | 62 | 52 | 45 | 41 | 51 | 45 | 41 | 50 | 45 | 41 | 49 | 44 | 41 | 39 | | | 39 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 93866 |
| 5° | 94311 |
| 10° | 94951 |
| 15° | 95913 |
| 20° | 94298 |
| 25° | 89974 |
| 30° | 81739 |
| 35° | 65938 |
| 40° | 45761 |
| 45° | 30038 |
| 50° | 20110 |
| 55° | 14322 |
| 60° | 12236 |
| 65° | 14038 |
| 70° | 15075 |
| 75° | 14535 |
| 80° | 13070 |
| 85° | 12029 |



TEST NUMBER: P579703

CATALOG NUMBER: HC410D010-HM40525830-41WDWB

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 72.6 | 6.3 |
| 10°-20° | 211.0 | 18.5 |
| 20°-30° | 301.4 | 26.4 |
| 30°-40° | 269.3 | 23.6 |
| 40°-50° | 138.1 | 12.1 |
| 50°-60° | 62.8 | 5.5 |
| 60°-70° | 46.8 | 4.1 |
| 70°-80° | 31.9 | 2.8 |
| 80°-90° | 9.4 | 0.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 585.0 | 51.2 |
| 0°-40° | 854.3 | 74.7 |
| 0°-60° | 1055.2 | 92.3 |
| 0°-90° | 1143.3 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1143.3 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 761 | |
| 5° | 762 | 73 |
| 15° | 751 | 211 |
| 25° | 661 | 301 |
| 35° | 438 | 269 |
| 45° | 172 | 138 |
| 55° | 67 | 63 |
| 65° | 48 | 47 |
| 75° | 30 | 32 |
| 85° | 8 | 9 |
| 90° | 0 | |



TEST NUMBER: P579703

CATALOG NUMBER: HC410D010-HM40525830-41WDWB

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 761.0 |
| 2.5° | 758.1 |
| 5° | 761.7 |
| 7.5° | 761.7 |
| 10° | 758.1 |
| 12.5° | 754.6 |
| 15° | 751.1 |
| 17.5° | 740.4 |
| 20° | 718.4 |
| 22.5° | 691.6 |
| 25° | 661.1 |
| 27.5° | 622.8 |
| 30° | 573.9 |
| 32.5° | 511.5 |
| 35° | 437.9 |
| 37.5° | 359.3 |
| 40° | 284.2 |
| 42.5° | 221.8 |
| 45° | 172.2 |
| 47.5° | 134.6 |
| 50° | 104.8 |
| 52.5° | 82.2 |
| 55° | 66.6 |
| 57.5° | 56.0 |
| 60° | 49.6 |
| 62.5° | 48.1 |
| 65° | 48.1 |
| 67.5° | 46.8 |
| 70° | 41.8 |
| 72.5° | 36.2 |
| 75° | 30.5 |
| 77.5° | 24.1 |
| 80° | 18.4 |
| 82.5° | 13.4 |
| 85° | 8.5 |
| 87.5° | 3.5 |
| 90° | 0.0 |



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)