

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579712

Luminaire Tested: **HC410D010-HM40525830-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579712
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC410D010-HM40525830-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 974.7 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579712

CATALOG NUMBER: HC410D010-HM40525830-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P579712

CATALOG NUMBER: HC410D010-HM40525830-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85639
5°	84988
10°	82789
15°	80602
20°	76985
25°	71723
30°	63166
35°	49811
40°	36148
45°	26567
50°	21626
55°	18128
60°	16430
65°	15089
70°	14029
75°	12867
80°	11578
85°	10048



TEST NUMBER: P579712

CATALOG NUMBER: HC410D010-HM40525830-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.7	6.6
10°-20°	177.0	18.2
20°-30°	240.0	24.6
30°-40°	205.9	21.1
40°-50°	121.6	12.5
50°-60°	77.1	7.9
60°-70°	51.7	5.3
70°-80°	28.6	2.9
80°-90°	8.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	481.8	49.4
0°-40°	687.7	70.6
0°-60°	886.3	90.9
0°-90°	974.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	974.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	694	
5°	686	65
15°	631	177
25°	527	240
35°	331	206
45°	152	122
55°	84	77
65°	52	52
75°	27	29
85°	7	8
90°	0	



TEST NUMBER: P579712

CATALOG NUMBER: HC410D010-HM40525830-41NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	694.3
2.5°	689.3
5°	686.4
7.5°	677.2
10°	661.0
12.5°	646.8
15°	631.2
17.5°	611.3
20°	586.5
22.5°	559.0
25°	527.0
27.5°	489.6
30°	443.5
32.5°	389.0
35°	330.8
37.5°	274.8
40°	224.5
42.5°	182.8
45°	152.3
47.5°	130.3
50°	112.7
52.5°	97.8
55°	84.3
57.5°	73.6
60°	66.6
62.5°	59.5
65°	51.7
67.5°	45.3
70°	38.9
72.5°	32.5
75°	27.0
77.5°	21.3
80°	16.3
82.5°	11.4
85°	7.1
87.5°	2.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)