

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579720

Luminaire Tested: **HC410D010-HM40525835-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579720
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC410D010-HM40525835-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 952.3 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579720

CATALOG NUMBER: HC410D010-HM40525835-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P579720

CATALOG NUMBER: HC410D010-HM40525835-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45	45	45	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94976
5°	95067
10°	95239
15°	96641
20°	94233
25°	88409
30°	78207
35°	59463
40°	37468
45°	21526
50°	11398
55°	4731
60°	1258
65°	1051
70°	793
75°	715
80°	497
85°	991



TEST NUMBER: P579720

CATALOG NUMBER: HC410D010-HM40525835-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	7.7
10°-20°	211.9	22.3
20°-30°	295.7	31.1
30°-40°	243.3	25.6
40°-50°	100.3	10.5
50°-60°	22.6	2.4
60°-70°	3.6	0.4
70°-80°	1.4	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	580.7	61.0
0°-40°	824.0	86.5
0°-60°	946.8	99.4
0°-90°	952.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	952.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	770	
5°	768	73
15°	757	212
25°	650	296
35°	395	243
45°	123	100
55°	22	23
65°	4	4
75°	2	1
85°	1	0
90°	0	



TEST NUMBER: P579720

CATALOG NUMBER: HC410D010-HM40525835-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	770.0
2.5°	766.3
5°	767.8
7.5°	764.8
10°	760.4
12.5°	758.2
15°	756.8
17.5°	743.6
20°	717.9
22.5°	685.5
25°	649.6
27.5°	606.3
30°	549.1
32.5°	478.5
35°	394.9
37.5°	310.4
40°	232.7
42.5°	169.6
45°	123.4
47.5°	88.1
50°	59.4
52.5°	37.4
55°	22.0
57.5°	11.0
60°	5.1
62.5°	4.4
65°	3.6
67.5°	3.0
70°	2.2
72.5°	1.5
75°	1.5
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)