

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592611

Luminaire Tested: **HC410D010-HM40525850-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592611
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC410D010-HM40525850-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1089.5 lumens
Efficiency: N/A
Efficacy: 110.1 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592611

CATALOG NUMBER: HC410D010-HM40525850-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P592611

CATALOG NUMBER: HC410D010-HM40525850-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92374
5°	91884
10°	90191
15°	88290
20°	84519
25°	78596
30°	69561
35°	54900
40°	41075
45°	31608
50°	25637
55°	21268
60°	18798
65°	17395
70°	16048
75°	14774
80°	13425
85°	10614



TEST NUMBER: P592611

CATALOG NUMBER: HC410D010-HM40525850-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.2	6.4
10°-20°	193.9	17.8
20°-30°	263.3	24.2
30°-40°	228.1	20.9
40°-50°	143.2	13.1
50°-60°	90.1	8.3
60°-70°	59.1	5.4
70°-80°	32.6	3.0
80°-90°	9.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.4	48.4
0°-40°	755.5	69.3
0°-60°	988.8	90.8
0°-90°	1089.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1089.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	749	
5°	742	70
15°	691	194
25°	578	263
35°	365	228
45°	181	143
55°	99	90
65°	60	59
75°	31	33
85°	8	9
90°	0	



TEST NUMBER: P592611

CATALOG NUMBER: HC410D010-HM40525850-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	748.9
2.5°	744.4
5°	742.1
7.5°	734.6
10°	720.1
12.5°	705.8
15°	691.4
17.5°	671.9
20°	643.9
22.5°	612.2
25°	577.5
27.5°	537.5
30°	488.4
32.5°	428.8
35°	364.6
37.5°	305.8
40°	255.1
42.5°	215.2
45°	181.2
47.5°	155.6
50°	133.6
52.5°	114.7
55°	98.9
57.5°	85.4
60°	76.2
62.5°	67.9
65°	59.6
67.5°	51.3
70°	44.5
72.5°	37.0
75°	31.0
77.5°	24.1
80°	18.9
82.5°	12.9
85°	7.5
87.5°	3.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)