

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579796

Luminaire Tested: **HC410D010-HM40525935-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579796
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC410D010-HM40525935-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1047.3 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579796

CATALOG NUMBER: HC410D010-HM40525935-41WDH

Luminous Intensity Polar Plot





TEST NUMBER: P579796

CATALOG NUMBER: HC410D010-HM40525935-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88044
5°	88715
10°	89816
15°	92069
20°	92749
25°	90096
30°	82594
35°	67955
40°	49545
45°	32166
50°	18134
55°	8623
60°	3404
65°	2101
70°	1443
75°	905
80°	497
85°	991



TEST NUMBER: P579796

CATALOG NUMBER: HC410D010-HM40525935-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.4	6.5
10°-20°	203.3	19.4
20°-30°	301.5	28.8
30°-40°	278.5	26.6
40°-50°	145.4	13.9
50°-60°	39.9	3.8
60°-70°	7.7	0.7
70°-80°	2.2	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	573.2	54.7
0°-40°	851.6	81.3
0°-60°	1036.9	99.0
0°-90°	1047.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1047.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	714	
5°	716	68
15°	721	203
25°	662	302
35°	451	278
45°	184	145
55°	40	40
65°	7	8
75°	2	2
85°	1	0
90°	0	



TEST NUMBER: P579796

CATALOG NUMBER: HC410D010-HM40525935-41WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	713.8
2.5°	711.8
5°	716.5
7.5°	718.4
10°	717.1
12.5°	718.4
15°	721.0
17.5°	718.4
20°	706.6
22.5°	687.6
25°	662.0
27.5°	627.2
30°	579.9
32.5°	520.3
35°	451.3
37.5°	379.2
40°	307.7
42.5°	242.1
45°	184.4
47.5°	135.2
50°	94.5
52.5°	62.9
55°	40.1
57.5°	23.7
60°	13.8
62.5°	9.8
65°	7.2
67.5°	5.2
70°	4.0
72.5°	2.6
75°	1.9
77.5°	1.4
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)