

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580138

Luminaire Tested: **HC425D010-HM40525830-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580138
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC425D010-HM40525830-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2308.9 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580138

CATALOG NUMBER: HC425D010-HM40525830-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P580138

CATALOG NUMBER: HC425D010-HM40525830-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	195750
5°	194727
10°	191167
15°	187127
20°	179120
25°	166555
30°	147426
35°	116351
40°	87078
45°	66984
50°	54344
55°	45052
60°	39865
65°	36862
70°	34044
75°	31263
80°	28413
85°	22644



TEST NUMBER: P580138

CATALOG NUMBER: HC425D010-HM40525830-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.7	6.4
10°-20°	411.0	17.8
20°-30°	558.0	24.2
30°-40°	483.4	20.9
40°-50°	303.5	13.1
50°-60°	190.9	8.3
60°-70°	125.4	5.4
70°-80°	69.2	3.0
80°-90°	18.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1117.6	48.4
0°-40°	1601.0	69.3
0°-60°	2095.4	90.8
0°-90°	2308.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2308.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1587	
5°	1573	149
15°	1465	411
25°	1224	558
35°	773	483
45°	384	304
55°	210	191
65°	126	125
75°	66	69
85°	16	19
90°	0	



TEST NUMBER: P580138

CATALOG NUMBER: HC425D010-HM40525830-41MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1587.0
2.5°	1577.4
5°	1572.7
7.5°	1556.7
10°	1526.3
12.5°	1495.8
15°	1465.4
17.5°	1423.9
20°	1364.6
22.5°	1297.4
25°	1223.8
27.5°	1139.0
30°	1035.1
32.5°	908.7
35°	772.7
37.5°	647.9
40°	540.8
42.5°	456.0
45°	384.0
47.5°	329.6
50°	283.2
52.5°	243.2
55°	209.5
57.5°	180.8
60°	161.6
62.5°	143.9
65°	126.3
67.5°	108.8
70°	94.4
72.5°	78.4
75°	65.6
77.5°	51.1
80°	40.0
82.5°	27.2
85°	16.0
87.5°	6.4
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)