

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580149

Luminaire Tested: **HC425D010-HM40525835-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC425D010-HM40525835-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2436.5 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580149

CATALOG NUMBER: HC425D010-HM40525835-41MDH

Luminous Intensity Polar Plot





TEST NUMBER: P580149

CATALOG NUMBER: HC425D010-HM40525835-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62	62	62	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58	58	58	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	315419
5°	308824
10°	291841
15°	272582
20°	249305
25°	222627
30°	186950
35°	131514
40°	81136
45°	48563
50°	28611
55°	14258
60°	7351
65°	4845
70°	2957
75°	2383
80°	1208
85°	2406



TEST NUMBER: P580149

CATALOG NUMBER: HC425D010-HM40525835-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.9	9.6
10°-20°	596.7	24.5
20°-30°	744.1	30.5
30°-40°	548.1	22.5
40°-50°	225.4	9.3
50°-60°	65.8	2.7
60°-70°	16.9	0.7
70°-80°	5.3	0.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1573.7	64.6
0°-40°	2121.9	87.1
0°-60°	2413.1	99.0
0°-90°	2436.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2436.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2557	
5°	2494	233
15°	2135	597
25°	1636	744
35°	873	548
45°	278	225
55°	66	66
65°	17	17
75°	5	5
85°	2	1
90°	0	



TEST NUMBER: P580149

CATALOG NUMBER: HC425D010-HM40525835-41MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2557.2
2.5°	2530.7
5°	2494.2
7.5°	2427.9
10°	2330.1
12.5°	2234.1
15°	2134.6
17.5°	2023.5
20°	1899.3
22.5°	1770.0
25°	1635.8
27.5°	1486.6
30°	1312.6
32.5°	1102.1
35°	873.4
37.5°	671.2
40°	503.9
42.5°	372.9
45°	278.4
47.5°	205.5
50°	149.1
52.5°	102.7
55°	66.3
57.5°	39.7
60°	29.8
62.5°	21.6
65°	16.6
67.5°	11.6
70°	8.2
72.5°	6.7
75°	5.0
77.5°	3.3
80°	1.7
82.5°	1.7
85°	1.7
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)