

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579836

Luminaire Tested: **HC415D010-HM40525827-41WDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579836  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC415D010-HM40525827-41WDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1509.0 lumens  
Efficiency: N/A  
Efficacy: 107.8 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579836

CATALOG NUMBER: HC415D010-HM40525827-41WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P579836

CATALOG NUMBER: HC415D010-HM40525827-41WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92	92	92	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85	85	85	85
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77	77	77	77
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71	71	71	71
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55	55	55	55
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51	51	51	51
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47	47	47	47
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	44	44	44	44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	121902
5°	123693
10°	127566
15°	136304
20°	144440
25°	142861
30°	128213
35°	99803
40°	67611
45°	42214
50°	18268
55°	6107
60°	1554
65°	1022
70°	649
75°	429
80°	639
85°	0



TEST NUMBER: P579836

CATALOG NUMBER: HC415D010-HM40525827-41WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.0	6.4
10°-20°	303.0	20.1
20°-30°	474.8	31.5
30°-40°	409.8	27.2
40°-50°	188.4	12.5
50°-60°	32.0	2.1
60°-70°	3.6	0.2
70°-80°	1.3	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	873.8	57.9
0°-40°	1283.6	85.1
0°-60°	1504.0	99.7
0°-90°	1509.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1509.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	988	
5°	999	96
15°	1067	303
25°	1050	475
35°	663	410
45°	242	188
55°	28	32
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P579836

CATALOG NUMBER: HC415D010-HM40525827-41WDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	988.3
2.5°	988.3
5°	999.0
7.5°	1008.7
10°	1018.5
12.5°	1039.0
15°	1067.4
17.5°	1091.5
20°	1100.4
22.5°	1087.0
25°	1049.7
27.5°	989.2
30°	900.2
32.5°	788.2
35°	662.8
37.5°	536.4
40°	419.9
42.5°	321.1
45°	242.0
47.5°	169.9
50°	95.2
52.5°	52.5
55°	28.4
57.5°	14.2
60°	6.3
62.5°	4.4
65°	3.5
67.5°	2.6
70°	1.8
72.5°	1.8
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)