

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580156

Luminaire Tested: **HC425D010-HM40525835-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580156
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC425D010-HM40525835-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2393.4 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580156

CATALOG NUMBER: HC425D010-HM40525835-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P580156

CATALOG NUMBER: HC425D010-HM40525835-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	202916
5°	201846
10°	198156
15°	193971
20°	185670
25°	172666
30°	152810
35°	120597
40°	90250
45°	69426
50°	56320
55°	46708
60°	41321
65°	38234
70°	35307
75°	32407
80°	29407
85°	23493



TEST NUMBER: P580156

CATALOG NUMBER: HC425D010-HM40525835-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.1	6.4
10°-20°	426.0	17.8
20°-30°	578.4	24.2
30°-40°	501.0	20.9
40°-50°	314.6	13.1
50°-60°	197.9	8.3
60°-70°	130.0	5.4
70°-80°	71.7	3.0
80°-90°	19.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1158.5	48.4
0°-40°	1659.6	69.3
0°-60°	2172.0	90.7
0°-90°	2393.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2393.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1645	
5°	1630	154
15°	1519	426
25°	1269	578
35°	801	501
45°	398	315
55°	217	198
65°	131	130
75°	68	72
85°	17	20
90°	0	



TEST NUMBER: P580156

CATALOG NUMBER: HC425D010-HM40525835-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1645.1
2.5°	1635.1
5°	1630.2
7.5°	1613.6
10°	1582.1
12.5°	1550.6
15°	1519.0
17.5°	1475.9
20°	1414.5
22.5°	1344.9
25°	1268.7
27.5°	1180.7
30°	1072.9
32.5°	941.9
35°	800.9
37.5°	671.6
40°	560.5
42.5°	472.6
45°	398.0
47.5°	341.6
50°	293.5
52.5°	252.1
55°	217.2
57.5°	187.4
60°	167.5
62.5°	149.3
65°	131.0
67.5°	112.8
70°	97.9
72.5°	81.3
75°	68.0
77.5°	53.1
80°	41.4
82.5°	28.2
85°	16.6
87.5°	6.7
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)