

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579866

Luminaire Tested: **HC415D010-HM40525835-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579866
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC415D010-HM40525835-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1467.5 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579866

CATALOG NUMBER: HC415D010-HM40525835-41MDH

Luminous Intensity Polar Plot





TEST NUMBER: P579866

CATALOG NUMBER: HC415D010-HM40525835-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62	62	62	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58	58	58	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	189977
5°	186010
10°	175786
15°	164180
20°	150150
25°	134083
30°	112603
35°	79219
40°	48868
45°	29253
50°	17232
55°	8580
60°	4440
65°	2919
70°	1803
75°	1430
80°	710
85°	1415



TEST NUMBER: P579866

CATALOG NUMBER: HC415D010-HM40525835-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.3	9.6
10°-20°	359.4	24.5
20°-30°	448.2	30.5
30°-40°	330.2	22.5
40°-50°	135.8	9.3
50°-60°	39.7	2.7
60°-70°	10.2	0.7
70°-80°	3.2	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	947.9	64.6
0°-40°	1278.0	87.1
0°-60°	1453.5	99.0
0°-90°	1467.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1467.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1540	
5°	1502	140
15°	1286	359
25°	985	448
35°	526	330
45°	168	136
55°	40	40
65°	10	10
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P579866

CATALOG NUMBER: HC415D010-HM40525835-41MDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1540.2
2.5°	1524.3
5°	1502.3
7.5°	1462.4
10°	1403.5
12.5°	1345.5
15°	1285.7
17.5°	1218.8
20°	1143.9
22.5°	1066.1
25°	985.2
27.5°	895.4
30°	790.6
32.5°	663.8
35°	526.1
37.5°	404.3
40°	303.5
42.5°	224.6
45°	167.7
47.5°	123.8
50°	89.8
52.5°	61.9
55°	39.9
57.5°	24.0
60°	18.0
62.5°	13.0
65°	10.0
67.5°	6.9
70°	5.0
72.5°	4.0
75°	3.0
77.5°	2.0
80°	1.0
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)