

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580174

Luminaire Tested: **HC425D010-HM40525840-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580174
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC425D010-HM40525840-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2459.4 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580174

CATALOG NUMBER: HC425D010-HM40525840-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P580174

CATALOG NUMBER: HC425D010-HM40525840-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	208516
5°	207406
10°	203629
15°	199335
20°	190802
25°	177429
30°	157040
35°	123925
40°	92745
45°	71345
50°	57894
55°	47998
60°	42456
65°	39284
70°	36280
75°	33312
80°	30260
85°	24059



TEST NUMBER: P580174

CATALOG NUMBER: HC425D010-HM40525840-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.4	6.4
10°-20°	437.8	17.8
20°-30°	594.4	24.2
30°-40°	514.9	20.9
40°-50°	323.3	13.1
50°-60°	203.4	8.3
60°-70°	133.6	5.4
70°-80°	73.7	3.0
80°-90°	20.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1190.5	48.4
0°-40°	1705.4	69.3
0°-60°	2232.0	90.8
0°-90°	2459.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2459.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1690	
5°	1675	158
15°	1561	438
25°	1304	594
35°	823	515
45°	409	323
55°	223	203
65°	135	134
75°	70	74
85°	17	20
90°	0	



TEST NUMBER: P580174

CATALOG NUMBER: HC425D010-HM40525840-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1690.5
2.5°	1680.3
5°	1675.1
7.5°	1658.0
10°	1625.8
12.5°	1593.4
15°	1561.0
17.5°	1516.7
20°	1453.6
22.5°	1382.0
25°	1303.7
27.5°	1213.3
30°	1102.6
32.5°	967.9
35°	823.0
37.5°	690.2
40°	576.0
42.5°	485.7
45°	409.0
47.5°	351.0
50°	301.7
52.5°	259.0
55°	223.2
57.5°	192.6
60°	172.1
62.5°	153.3
65°	134.6
67.5°	115.8
70°	100.6
72.5°	83.5
75°	69.9
77.5°	54.5
80°	42.6
82.5°	29.0
85°	17.0
87.5°	6.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)