

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592697

Luminaire Tested: **HC4R25D010-HM40525850-42RMDC**

Issue Date: 9/23/2021

Test Information

Test Method: LM-41-14
Report Number: P592697
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/23/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC4R25D010-HM40525850-42RMDC
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2641.7 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592697

CATALOG NUMBER: HC4R25D010-HM40525850-42RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P592697

CATALOG NUMBER: HC4R25D010-HM40525850-42RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80																			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74																			
5	92	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69																			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64																			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60																			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56																			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52																			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	299360
5°	305778
10°	317855
15°	317965
20°	293987
25°	254052
30°	206676
35°	151827
40°	87754
45°	41010
50°	18959
55°	6602
60°	2097
65°	1488
70°	1226
75°	810
80°	0
85°	0



TEST NUMBER: P592697

CATALOG NUMBER: HC4R25D010-HM40525850-42RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.2	9.0
10°-20°	690.1	26.1
20°-30°	849.9	32.2
30°-40°	620.4	23.5
40°-50°	202.2	7.7
50°-60°	33.8	1.3
60°-70°	5.2	0.2
70°-80°	1.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1778.2	67.3
0°-40°	2398.7	90.8
0°-60°	2634.7	99.7
0°-90°	2641.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2641.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2427	
5°	2470	238
15°	2490	690
25°	1867	850
35°	1008	620
45°	235	202
55°	31	34
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P592697

CATALOG NUMBER: HC4R25D010-HM40525850-42RMDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2427.0
2.5°	2428.7
5°	2469.6
7.5°	2517.3
10°	2537.8
12.5°	2530.9
15°	2490.0
17.5°	2387.8
20°	2239.7
22.5°	2060.9
25°	1866.7
27.5°	1664.0
30°	1451.1
32.5°	1233.1
35°	1008.3
37.5°	781.7
40°	545.0
42.5°	356.0
45°	235.1
47.5°	155.0
50°	98.8
52.5°	57.9
55°	30.7
57.5°	12.0
60°	8.5
62.5°	6.8
65°	5.1
67.5°	3.4
70°	3.4
72.5°	1.7
75°	1.7
77.5°	1.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)