

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579918

Luminaire Tested: **HC415D010-HM40525930-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579918
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC415D010-HM40525930-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1097.7 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579918

CATALOG NUMBER: HC415D010-HM40525930-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P579918

CATALOG NUMBER: HC415D010-HM40525930-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109469
5°	109578
10°	109793
15°	111390
20°	108619
25°	101909
30°	90142
35°	68558
40°	43185
45°	24788
50°	13164
55°	5462
60°	1455
65°	1226
70°	902
75°	810
80°	568
85°	1132



TEST NUMBER: P579918

CATALOG NUMBER: HC415D010-HM40525930-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.2	7.7
10°-20°	244.3	22.3
20°-30°	340.9	31.1
30°-40°	280.5	25.6
40°-50°	115.6	10.5
50°-60°	26.1	2.4
60°-70°	4.2	0.4
70°-80°	1.5	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	669.3	61.0
0°-40°	949.9	86.5
0°-60°	1091.5	99.4
0°-90°	1097.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1097.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	888	
5°	885	84
15°	872	244
25°	749	341
35°	455	281
45°	142	116
55°	25	26
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P579918

CATALOG NUMBER: HC415D010-HM40525930-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	887.5
2.5°	883.3
5°	885.0
7.5°	881.6
10°	876.6
12.5°	874.0
15°	872.3
17.5°	857.1
20°	827.5
22.5°	790.2
25°	748.8
27.5°	698.9
30°	632.9
32.5°	551.7
35°	455.3
37.5°	357.9
40°	268.2
42.5°	195.5
45°	142.1
47.5°	101.5
50°	68.6
52.5°	43.2
55°	25.4
57.5°	12.7
60°	5.9
62.5°	5.1
65°	4.2
67.5°	3.4
70°	2.5
72.5°	1.7
75°	1.7
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)