

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580211

Luminaire Tested: **HC425D010-HM40525930-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580211
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC425D010-HM40525930-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1933.6 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580211

CATALOG NUMBER: HC425D010-HM40525930-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P580211

CATALOG NUMBER: HC425D010-HM40525930-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	169884
5°	168614
10°	164226
15°	159902
20°	152749
25°	142303
30°	125293
35°	98824
40°	71733
45°	52697
50°	42869
55°	35956
60°	32588
65°	29945
70°	27877
75°	25449
80°	22943
85°	19813



TEST NUMBER: P580211

CATALOG NUMBER: HC425D010-HM40525930-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	6.6
10°-20°	351.2	18.2
20°-30°	476.1	24.6
30°-40°	408.5	21.1
40°-50°	241.2	12.5
50°-60°	152.9	7.9
60°-70°	102.7	5.3
70°-80°	56.7	2.9
80°-90°	15.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	955.7	49.4
0°-40°	1364.3	70.6
0°-60°	1758.3	90.9
0°-90°	1933.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1933.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1377	
5°	1362	128
15°	1252	351
25°	1046	476
35°	656	409
45°	302	241
55°	167	153
65°	103	103
75°	53	57
85°	14	16
90°	0	



TEST NUMBER: P580211

CATALOG NUMBER: HC425D010-HM40525930-41NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1377.3
2.5°	1367.4
5°	1361.8
7.5°	1343.5
10°	1311.2
12.5°	1283.1
15°	1252.2
17.5°	1212.8
20°	1163.7
22.5°	1108.8
25°	1045.6
27.5°	971.1
30°	879.7
32.5°	771.6
35°	656.3
37.5°	545.3
40°	445.5
42.5°	362.6
45°	302.1
47.5°	258.5
50°	223.4
52.5°	194.0
55°	167.2
57.5°	146.2
60°	132.1
62.5°	118.1
65°	102.6
67.5°	90.0
70°	77.3
72.5°	64.7
75°	53.4
77.5°	42.1
80°	32.3
82.5°	22.5
85°	14.0
87.5°	5.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)