

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592712

Luminaire Tested: **HC425D010-HM40525950-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592712
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC425D010-HM40525950-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2254.7 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592712

CATALOG NUMBER: HC425D010-HM40525950-41MDH

Luminous Intensity Polar Plot





TEST NUMBER: P592712

CATALOG NUMBER: HC425D010-HM40525950-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86			86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79			79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67			67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62			62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58			58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54			54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51			51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47			47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	291885
5°	285782
10°	270073
15°	252239
20°	230692
25°	206010
30°	173006
35°	121712
40°	75082
45°	44935
50°	26500
55°	13182
60°	6833
65°	4495
70°	2777
75°	2192
80°	1137
85°	2264



TEST NUMBER: P592712

CATALOG NUMBER: HC425D010-HM40525950-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.5	9.6
10°-20°	552.2	24.5
20°-30°	688.6	30.5
30°-40°	507.3	22.5
40°-50°	208.6	9.3
50°-60°	61.0	2.7
60°-70°	15.7	0.7
70°-80°	4.8	0.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1456.3	64.6
0°-40°	1963.6	87.1
0°-60°	2233.1	99.0
0°-90°	2254.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2254.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2366	
5°	2308	216
15°	1975	552
25°	1514	689
35°	808	507
45°	258	209
55°	61	61
65°	15	16
75°	5	5
85°	2	1
90°	0	



TEST NUMBER: P592712

CATALOG NUMBER: HC425D010-HM40525950-41MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2366.4
2.5°	2341.9
5°	2308.1
7.5°	2246.8
10°	2156.3
12.5°	2067.3
15°	1975.3
17.5°	1872.6
20°	1757.5
22.5°	1638.0
25°	1513.7
27.5°	1375.7
30°	1214.7
32.5°	1019.8
35°	808.3
37.5°	621.2
40°	466.3
42.5°	345.0
45°	257.6
47.5°	190.1
50°	138.1
52.5°	95.1
55°	61.3
57.5°	36.8
60°	27.7
62.5°	20.0
65°	15.4
67.5°	10.7
70°	7.7
72.5°	6.1
75°	4.6
77.5°	3.0
80°	1.6
82.5°	1.6
85°	1.6
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)