

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592717

Luminaire Tested: **HC425D010-HM40525950-41NDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592717
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC425D010-HM40525950-41NDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2270.0 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592717

CATALOG NUMBER: HC425D010-HM40525950-41NDC

Luminous Intensity Polar Plot





TEST NUMBER: P592717

CATALOG NUMBER: HC425D010-HM40525950-41NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81		
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76		
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62		
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58		
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55		
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	334341
5°	333909
10°	327412
15°	304442
20°	261815
25°	210338
30°	164204
35°	114966
40°	59012
45°	29951
50°	15006
55°	5613
60°	2245
65°	1780
70°	1082
75°	763
80°	1137
85°	0



TEST NUMBER: P592717

CATALOG NUMBER: HC425D010-HM40525950-41NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.0	11.2
10°-20°	658.1	29.0
20°-30°	708.9	31.2
30°-40°	465.8	20.5
40°-50°	144.8	6.4
50°-60°	28.4	1.3
60°-70°	6.0	0.3
70°-80°	2.2	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1622.0	71.5
0°-40°	2087.8	92.0
0°-60°	2261.1	99.6
0°-90°	2270.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2270.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2711	
5°	2697	255
15°	2384	658
25°	1546	709
35°	764	466
45°	172	145
55°	26	28
65°	6	6
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P592717

CATALOG NUMBER: HC425D010-HM40525950-41NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2710.6
2.5°	2696.8
5°	2696.8
7.5°	2675.4
10°	2614.1
12.5°	2516.0
15°	2384.1
17.5°	2207.8
20°	1994.6
22.5°	1764.6
25°	1545.5
27.5°	1341.5
30°	1152.9
32.5°	975.1
35°	763.5
37.5°	532.0
40°	366.5
42.5°	253.0
45°	171.7
47.5°	116.5
50°	78.2
52.5°	49.1
55°	26.1
57.5°	10.7
60°	9.1
62.5°	7.7
65°	6.1
67.5°	4.6
70°	3.0
72.5°	3.0
75°	1.6
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)