

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580265

Luminaire Tested: **HC430D010-HM43040827-41NDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580265  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC430D010-HM43040827-41NDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2495.5 lumens  
Efficiency: N/A  
Efficacy: 89.1 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580265

CATALOG NUMBER: HC430D010-HM43040827-41NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P580265

CATALOG NUMBER: HC430D010-HM43040827-41NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	219247
5°	217608
10°	211945
15°	206371
20°	197129
25°	183649
30°	161712
35°	127539
40°	92568
45°	68013
50°	55342
55°	46407
60°	42036
65°	38642
70°	35956
75°	32836
80°	29620
85°	25757



TEST NUMBER: P580265

CATALOG NUMBER: HC430D010-HM43040827-41NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	165.7	6.6
10°-20°	453.3	18.2
20°-30°	614.5	24.6
30°-40°	527.3	21.1
40°-50°	311.3	12.5
50°-60°	197.3	7.9
60°-70°	132.5	5.3
70°-80°	73.2	2.9
80°-90°	20.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1233.5	49.4
0°-40°	1760.7	70.6
0°-60°	2269.3	90.9
0°-90°	2495.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2495.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1778	
5°	1758	166
15°	1616	453
25°	1349	614
35°	847	527
45°	390	311
55°	216	197
65°	132	133
75°	69	73
85°	18	20
90°	0	



TEST NUMBER: P580265

CATALOG NUMBER: HC430D010-HM43040827-41NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1777.5
2.5°	1764.8
5°	1757.5
7.5°	1734.0
10°	1692.2
12.5°	1656.0
15°	1616.1
17.5°	1565.3
20°	1501.8
22.5°	1431.1
25°	1349.4
27.5°	1253.3
30°	1135.4
32.5°	995.8
35°	847.0
37.5°	703.8
40°	574.9
42.5°	468.0
45°	389.9
47.5°	333.8
50°	288.4
52.5°	250.3
55°	215.8
57.5°	188.6
60°	170.4
62.5°	152.4
65°	132.4
67.5°	116.1
70°	99.7
72.5°	83.5
75°	68.9
77.5°	54.4
80°	41.7
82.5°	29.0
85°	18.2
87.5°	7.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)