

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579996

Luminaire Tested: **HC420D010-HM40525830-41MDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579996  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC420D010-HM40525830-41MDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2022.4 lumens  
Efficiency: N/A  
Efficacy: 101.1 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.96  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579996

CATALOG NUMBER: HC420D010-HM40525830-41MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P579996

CATALOG NUMBER: HC420D010-HM40525830-41MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	91	83	77	72	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52			
10	71	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	234270
5°	238570
10°	245925
15°	243199
20°	223315
25°	192659
30°	157012
35°	116246
40°	66693
45°	32236
50°	15332
55°	5355
60°	1949
65°	1138
70°	938
75°	620
80°	0
85°	0



TEST NUMBER: P579996

CATALOG NUMBER: HC420D010-HM40525830-41MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	185.3	9.2
10°-20°	528.0	26.1
20°-30°	644.8	31.9
30°-40°	474.0	23.4
40°-50°	157.1	7.8
50°-60°	27.7	1.4
60°-70°	4.2	0.2
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1358.1	67.2
0°-40°	1832.1	90.6
0°-60°	2016.9	99.7
0°-90°	2022.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2022.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1899	
5°	1927	185
15°	1904	528
25°	1416	645
35°	772	474
45°	185	157
55°	25	28
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P579996

CATALOG NUMBER: HC420D010-HM40525830-41MDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1899.3
2.5°	1900.6
5°	1926.8
7.5°	1955.6
10°	1963.5
12.5°	1945.2
15°	1904.5
17.5°	1820.6
20°	1701.3
22.5°	1562.4
25°	1415.6
27.5°	1262.3
30°	1102.4
32.5°	942.4
35°	772.0
37.5°	599.0
40°	414.2
42.5°	273.9
45°	184.8
47.5°	123.2
50°	79.9
52.5°	47.1
55°	24.9
57.5°	10.4
60°	7.9
62.5°	5.3
65°	3.9
67.5°	2.6
70°	2.6
72.5°	1.3
75°	1.3
77.5°	1.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)