

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P571728

Luminaire Tested: **HC420D010-HM40525835-41NDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P571728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC420D010-HM40525835-41NDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2009.6 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P571728

CATALOG NUMBER: HC420D010-HM40525835-41NDC

Luminous Intensity Polar Plot





TEST NUMBER: P571728

CATALOG NUMBER: HC420D010-HM40525835-41NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	295980
5°	295600
10°	289837
15°	269504
20°	231782
25°	186194
30°	145361
35°	101775
40°	52234
45°	26514
50°	13279
55°	4968
60°	1998
65°	1576
70°	1010
75°	667
80°	994
85°	0



TEST NUMBER: P571728

CATALOG NUMBER: HC420D010-HM40525835-41NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	225.7	11.2
10°-20°	582.6	29.0
20°-30°	627.6	31.2
30°-40°	412.3	20.5
40°-50°	128.2	6.4
50°-60°	25.2	1.3
60°-70°	5.3	0.3
70°-80°	2.0	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1435.9	71.5
0°-40°	1848.3	92.0
0°-60°	2001.6	99.6
0°-90°	2009.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2009.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2400	
5°	2387	226
15°	2110	583
25°	1368	628
35°	676	412
45°	152	128
55°	23	25
65°	5	5
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P571728

CATALOG NUMBER: HC420D010-HM40525835-41NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2399.6
2.5°	2387.4
5°	2387.4
7.5°	2368.4
10°	2314.1
12.5°	2227.2
15°	2110.5
17.5°	1954.5
20°	1765.8
22.5°	1562.2
25°	1368.1
27.5°	1187.6
30°	1020.6
32.5°	863.2
35°	675.9
37.5°	471.0
40°	324.4
42.5°	223.9
45°	152.0
47.5°	103.1
50°	69.2
52.5°	43.5
55°	23.1
57.5°	9.5
60°	8.1
62.5°	6.8
65°	5.4
67.5°	4.0
70°	2.8
72.5°	2.8
75°	1.4
77.5°	1.4
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)