

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580274

Luminaire Tested: **HC430D010-HM43040830-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580274
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC430D010-HM43040830-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3166.8 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580274

CATALOG NUMBER: HC430D010-HM43040830-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P580274

CATALOG NUMBER: HC430D010-HM43040830-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80			
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72			
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65			
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59			
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54			
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49			
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	259988
5°	261216
10°	263009
15°	265648
20°	261211
25°	249207
30°	226417
35°	182620
40°	126720
45°	83189
50°	55745
55°	39655
60°	33895
65°	38934
70°	41762
75°	40223
80°	36226
85°	33399



TEST NUMBER: P580274

CATALOG NUMBER: HC430D010-HM43040830-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.1	6.3
10°-20°	584.4	18.5
20°-30°	835.0	26.4
30°-40°	745.9	23.6
40°-50°	382.6	12.1
50°-60°	173.9	5.5
60°-70°	129.7	4.1
70°-80°	88.3	2.8
80°-90°	26.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1620.4	51.2
0°-40°	2366.3	74.7
0°-60°	2922.7	92.3
0°-90°	3166.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3166.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2108	
5°	2110	201
15°	2080	584
25°	1831	835
35°	1213	746
45°	477	383
55°	184	174
65°	133	130
75°	84	88
85°	24	26
90°	0	



TEST NUMBER: P580274

CATALOG NUMBER: HC430D010-HM43040830-41WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2107.8
2.5°	2099.9
5°	2109.7
7.5°	2109.7
10°	2099.9
12.5°	2090.1
15°	2080.3
17.5°	2050.8
20°	1990.0
22.5°	1915.5
25°	1831.1
27.5°	1725.1
30°	1589.7
32.5°	1417.0
35°	1212.8
37.5°	995.0
40°	787.0
42.5°	614.3
45°	476.9
47.5°	372.9
50°	290.5
52.5°	227.6
55°	184.4
57.5°	155.0
60°	137.4
62.5°	133.4
65°	133.4
67.5°	129.5
70°	115.8
72.5°	100.1
75°	84.4
77.5°	66.8
80°	51.0
82.5°	37.3
85°	23.6
87.5°	9.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)