

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580279

Luminaire Tested: **HC430D010-HM43040830-41MDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580279
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC430D010-HM43040830-41MDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3029.4 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580279

CATALOG NUMBER: HC430D010-HM43040830-41MDC

Luminous Intensity Polar Plot





TEST NUMBER: P580279

CATALOG NUMBER: HC430D010-HM43040830-41MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	91	83	77	72	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	350906
5°	357348
10°	368368
15°	364281
20°	334520
25°	288580
30°	235176
35°	174127
40°	99895
45°	48284
50°	22989
55°	8021
60°	2886
65°	1722
70°	1406
75°	905
80°	0
85°	0



TEST NUMBER: P580279

CATALOG NUMBER: HC430D010-HM43040830-41MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.6	9.2
10°-20°	790.9	26.1
20°-30°	965.8	31.9
30°-40°	710.0	23.4
40°-50°	235.3	7.8
50°-60°	41.6	1.4
60°-70°	6.3	0.2
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2034.3	67.2
0°-40°	2744.3	90.6
0°-60°	3021.2	99.7
0°-90°	3029.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3029.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2845	
5°	2886	278
15°	2853	791
25°	2120	966
35°	1156	710
45°	277	235
55°	37	42
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P580279

CATALOG NUMBER: HC430D010-HM43040830-41MDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2844.9
2.5°	2846.8
5°	2886.1
7.5°	2929.3
10°	2941.1
12.5°	2913.6
15°	2852.7
17.5°	2727.2
20°	2548.5
22.5°	2340.4
25°	2120.4
27.5°	1890.8
30°	1651.2
32.5°	1411.7
35°	1156.4
37.5°	897.2
40°	620.4
42.5°	410.4
45°	276.8
47.5°	184.5
50°	119.8
52.5°	70.7
55°	37.3
57.5°	15.7
60°	11.7
62.5°	7.9
65°	5.9
67.5°	3.9
70°	3.9
72.5°	1.9
75°	1.9
77.5°	1.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)