

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580282

Luminaire Tested: **HC430D010-HM43040830-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580282
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC430D010-HM43040830-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2833.3 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580282

CATALOG NUMBER: HC430D010-HM43040830-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P580282

CATALOG NUMBER: HC430D010-HM43040830-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	240203
5°	238942
10°	234565
15°	229637
20°	219798
25°	204390
30°	180897
35°	142777
40°	106834
45°	82195
50°	66663
55°	55310
60°	48919
65°	45268
70°	41762
75°	38364
80°	34877
85°	27739



TEST NUMBER: P580282

CATALOG NUMBER: HC430D010-HM43040830-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.4	6.4
10°-20°	504.3	17.8
20°-30°	684.7	24.2
30°-40°	593.1	20.9
40°-50°	372.4	13.1
50°-60°	234.3	8.3
60°-70°	153.9	5.4
70°-80°	84.9	3.0
80°-90°	23.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1371.5	48.4
0°-40°	1964.6	69.3
0°-60°	2571.3	90.8
0°-90°	2833.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2833.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1947	
5°	1930	182
15°	1798	504
25°	1502	685
35°	948	593
45°	471	372
55°	257	234
65°	155	154
75°	80	85
85°	20	23
90°	0	



TEST NUMBER: P580282

CATALOG NUMBER: HC430D010-HM43040830-41MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1947.4
2.5°	1935.6
5°	1929.8
7.5°	1910.2
10°	1872.8
12.5°	1835.5
15°	1798.3
17.5°	1747.2
20°	1674.5
22.5°	1592.1
25°	1501.8
27.5°	1397.7
30°	1270.1
32.5°	1115.0
35°	948.2
37.5°	795.0
40°	663.5
42.5°	559.5
45°	471.2
47.5°	404.4
50°	347.4
52.5°	298.4
55°	257.2
57.5°	221.9
60°	198.3
62.5°	176.6
65°	155.1
67.5°	133.4
70°	115.8
72.5°	96.2
75°	80.5
77.5°	62.8
80°	49.1
82.5°	33.4
85°	19.6
87.5°	7.9
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)