

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580046

Luminaire Tested: **HC420D010-HM40525927-41NDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580046
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC420D010-HM40525927-41NDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1531.3 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580046

CATALOG NUMBER: HC420D010-HM40525927-41NDC

Luminous Intensity Polar Plot





TEST NUMBER: P580046

CATALOG NUMBER: HC420D010-HM40525927-41NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94	94	94	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87	87	87	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81	81	81	81
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76	76	76	76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71	71	71	71
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62	62	62	62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58	58	58	58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55	55	55	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	225562
5°	225260
10°	220863
15°	205375
20°	176613
25°	141881
30°	110780
35°	77562
40°	39803
45°	20200
50°	10132
55°	3763
60°	1529
65°	1197
70°	757
75°	477
80°	710
85°	0



TEST NUMBER: P580046

CATALOG NUMBER: HC420D010-HM40525927-41NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.0	11.2
10°-20°	443.9	29.0
20°-30°	478.3	31.2
30°-40°	314.2	20.5
40°-50°	97.7	6.4
50°-60°	19.2	1.3
60°-70°	4.1	0.3
70°-80°	1.5	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1094.2	71.5
0°-40°	1408.4	92.0
0°-60°	1525.3	99.6
0°-90°	1531.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1531.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1829	
5°	1819	172
15°	1608	444
25°	1042	478
35°	515	314
45°	116	98
55°	18	19
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P580046

CATALOG NUMBER: HC420D010-HM40525927-41NDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	1828.7
2.5°	1819.3
5°	1819.3
7.5°	1804.8
10°	1763.4
12.5°	1697.2
15°	1608.3
17.5°	1489.4
20°	1345.5
22.5°	1190.5
25°	1042.5
27.5°	905.0
30°	777.8
32.5°	657.8
35°	515.1
37.5°	358.9
40°	247.2
42.5°	170.7
45°	115.8
47.5°	78.6
50°	52.8
52.5°	33.1
55°	17.5
57.5°	7.2
60°	6.2
62.5°	5.2
65°	4.1
67.5°	3.1
70°	2.1
72.5°	2.1
75°	1.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)