

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580333

Luminaire Tested: **HC430D010-HM43040927-41MDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580333
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC430D010-HM43040927-41MDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2419.8 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580333

CATALOG NUMBER: HC430D010-HM43040927-41MDC

Luminous Intensity Polar Plot





TEST NUMBER: P580333

CATALOG NUMBER: HC430D010-HM43040927-41MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	91	83	77	72	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	64	60	57	56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	280291
5°	285435
10°	294234
15°	290970
20°	267183
25°	230507
30°	187847
35°	139088
40°	79784
45°	38568
50°	18364
55°	6408
60°	2319
65°	1372
70°	1154
75°	763
80°	0
85°	0



TEST NUMBER: P580333

CATALOG NUMBER: HC430D010-HM43040927-41MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.7	9.2
10°-20°	631.7	26.1
20°-30°	771.4	31.9
30°-40°	567.1	23.4
40°-50°	188.0	7.8
50°-60°	33.2	1.4
60°-70°	5.0	0.2
70°-80°	1.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1624.8	67.1
0°-40°	2191.9	90.6
0°-60°	2413.1	99.7
0°-90°	2419.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2419.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2272	
5°	2305	222
15°	2279	632
25°	1694	771
35°	924	567
45°	221	188
55°	30	33
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P580333

CATALOG NUMBER: HC430D010-HM43040927-41MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2272.4
2.5°	2273.9
5°	2305.3
7.5°	2339.7
10°	2349.2
12.5°	2327.2
15°	2278.6
17.5°	2178.2
20°	2035.5
22.5°	1869.3
25°	1693.7
27.5°	1510.2
30°	1318.9
32.5°	1127.5
35°	923.7
37.5°	716.6
40°	495.5
42.5°	327.8
45°	221.1
47.5°	147.4
50°	95.7
52.5°	56.4
55°	29.8
57.5°	12.5
60°	9.4
62.5°	6.3
65°	4.7
67.5°	3.2
70°	3.2
72.5°	1.6
75°	1.6
77.5°	1.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)