

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580368

Luminaire Tested: **HC4R30D010-HM43040935-42RMDC**

Issue Date: 9/23/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580368  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-13)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/23/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC4R30D010-HM43040935-42RMDC  
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2721.1 lumens  
Efficiency: N/A  
Efficacy: 97.2 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.96  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580368

CATALOG NUMBER: HC4R30D010-HM43040935-42RMDC

### Luminous Intensity Polar Plot





TEST NUMBER: P580368

CATALOG NUMBER: HC4R30D010-HM43040935-42RMDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	308352
5°	314965
10°	327387
15°	327517
20°	302808
25°	261673
30°	212886
35°	156374
40°	90395
45°	42231
50°	19515
55°	6795
60°	2171
65°	1547
70°	1262
75°	858
80°	0
85°	0



TEST NUMBER: P580368

CATALOG NUMBER: HC4R30D010-HM43040935-42RMDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	245.4	9.0
10°-20°	710.8	26.1
20°-30°	875.4	32.2
30°-40°	639.1	23.5
40°-50°	208.3	7.7
50°-60°	34.8	1.3
60°-70°	5.4	0.2
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1831.6	67.3
0°-40°	2470.7	90.8
0°-60°	2713.8	99.7
0°-90°	2721.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2721.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2500	
5°	2544	245
15°	2565	711
25°	1923	875
35°	1038	639
45°	242	208
55°	32	35
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P580368

CATALOG NUMBER: HC4R30D010-HM43040935-42RMDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2499.9
2.5°	2501.7
5°	2543.8
7.5°	2592.8
10°	2613.9
12.5°	2606.9
15°	2564.8
17.5°	2459.5
20°	2306.9
22.5°	2122.7
25°	1922.7
27.5°	1714.0
30°	1494.7
32.5°	1270.1
35°	1038.5
37.5°	805.3
40°	561.4
42.5°	366.6
45°	242.1
47.5°	159.6
50°	101.7
52.5°	59.7
55°	31.6
57.5°	12.3
60°	8.8
62.5°	7.0
65°	5.3
67.5°	3.5
70°	3.5
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)