

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580097

Luminaire Tested: **HC420D010-HM40525940-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580097
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC420D010-HM40525940-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2006.6 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580097

CATALOG NUMBER: HC420D010-HM40525940-41WDH

Luminous Intensity Polar Plot





TEST NUMBER: P580097

CATALOG NUMBER: HC420D010-HM40525940-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	168712
5°	169976
10°	172091
15°	176426
20°	177715
25°	172639
30°	158279
35°	130249
40°	94935
45°	61629
50°	34732
55°	16494
60°	6513
65°	4057
70°	2741
75°	1811
80°	923
85°	1840



TEST NUMBER: P580097

CATALOG NUMBER: HC420D010-HM40525940-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.1	6.5
10°-20°	389.5	19.4
20°-30°	577.7	28.8
30°-40°	533.6	26.6
40°-50°	278.6	13.9
50°-60°	76.4	3.8
60°-70°	14.7	0.7
70°-80°	4.1	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1098.3	54.7
0°-40°	1631.9	81.3
0°-60°	1986.9	99.0
0°-90°	2006.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2006.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1368	
5°	1373	131
15°	1382	389
25°	1268	578
35°	865	534
45°	353	279
55°	77	76
65°	14	15
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P580097

CATALOG NUMBER: HC420D010-HM40525940-41WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1367.8
2.5°	1364.0
5°	1372.8
7.5°	1376.5
10°	1374.0
12.5°	1376.5
15°	1381.6
17.5°	1376.5
20°	1353.9
22.5°	1317.4
25°	1268.5
27.5°	1201.8
30°	1111.3
32.5°	996.9
35°	865.0
37.5°	726.6
40°	589.6
42.5°	463.8
45°	353.3
47.5°	259.0
50°	181.0
52.5°	120.7
55°	76.7
57.5°	45.3
60°	26.4
62.5°	18.8
65°	13.9
67.5°	10.1
70°	7.6
72.5°	5.0
75°	3.8
77.5°	2.5
80°	1.3
82.5°	1.3
85°	1.3
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)