

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580100

Luminaire Tested: **HC420D010-HM40525940-41NDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580100  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC420D010-HM40525940-41NDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1859.6 lumens  
Efficiency: N/A  
Efficacy: 93.0 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580100

CATALOG NUMBER: HC420D010-HM40525940-41NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P580100

CATALOG NUMBER: HC420D010-HM40525940-41NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	273901
5°	273536
10°	268207
15°	249392
20°	214482
25°	172312
30°	134508
35°	94186
40°	48337
45°	24526
50°	12281
55°	4580
60°	1875
65°	1459
70°	902
75°	620
80°	923
85°	0



TEST NUMBER: P580100

CATALOG NUMBER: HC420D010-HM40525940-41NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	208.9	11.2
10°-20°	539.1	29.0
20°-30°	580.8	31.2
30°-40°	381.6	20.5
40°-50°	118.6	6.4
50°-60°	23.3	1.3
60°-70°	5.0	0.3
70°-80°	1.8	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1328.7	71.5
0°-40°	1710.3	92.0
0°-60°	1852.2	99.6
0°-90°	1859.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1859.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2221	
5°	2209	209
15°	1953	539
25°	1266	581
35°	626	382
45°	141	119
55°	21	23
65°	5	5
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P580100

CATALOG NUMBER: HC420D010-HM40525940-41NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2220.6
2.5°	2209.2
5°	2209.2
7.5°	2191.7
10°	2141.4
12.5°	2061.0
15°	1953.0
17.5°	1808.6
20°	1634.0
22.5°	1445.6
25°	1266.1
27.5°	1098.9
30°	944.4
32.5°	798.8
35°	625.5
37.5°	435.9
40°	300.2
42.5°	207.3
45°	140.6
47.5°	95.4
50°	64.0
52.5°	40.1
55°	21.3
57.5°	8.8
60°	7.6
62.5°	6.3
65°	5.0
67.5°	3.8
70°	2.5
72.5°	2.5
75°	1.3
77.5°	1.3
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)