

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580437

Luminaire Tested: **HC435D010-HM43040835-41MDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580437  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC435D010-HM43040835-41MDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3464.6 lumens  
Efficiency: N/A  
Efficacy: 102.8 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580437

CATALOG NUMBER: HC435D010-HM43040835-41MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P580437

CATALOG NUMBER: HC435D010-HM43040835-41MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62	62	62	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58	58	58	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47	47	47	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	448522
5°	439141
10°	414986
15°	387585
20°	354485
25°	316561
30°	265826
35°	187002
40°	115352
45°	69060
50°	40700
55°	20279
60°	10460
65°	6888
70°	4256
75°	3384
80°	1705
85°	3397



TEST NUMBER: P580437

CATALOG NUMBER: HC435D010-HM43040835-41MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	331.2	9.6
10°-20°	848.5	24.5
20°-30°	1058.1	30.5
30°-40°	779.4	22.5
40°-50°	320.5	9.3
50°-60°	93.6	2.7
60°-70°	24.1	0.7
70°-80°	7.4	0.2
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2237.8	64.6
0°-40°	3017.2	87.1
0°-60°	3431.4	99.0
0°-90°	3464.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3464.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3636	
5°	3547	331
15°	3035	848
25°	2326	1058
35°	1242	779
45°	396	321
55°	94	94
65°	24	24
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P580437

CATALOG NUMBER: HC435D010-HM43040835-41MDH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3636.3
2.5°	3598.5
5°	3546.7
7.5°	3452.4
10°	3313.3
12.5°	3176.6
15°	3035.2
17.5°	2877.4
20°	2700.6
22.5°	2516.9
25°	2326.0
27.5°	2113.9
30°	1866.4
32.5°	1567.2
35°	1241.9
37.5°	954.4
40°	716.4
42.5°	530.2
45°	395.9
47.5°	292.2
50°	212.1
52.5°	146.1
55°	94.3
57.5°	56.5
60°	42.4
62.5°	30.7
65°	23.6
67.5°	16.5
70°	11.8
72.5°	9.4
75°	7.1
77.5°	4.7
80°	2.4
82.5°	2.4
85°	2.4
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)