

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580129

Luminaire Tested: **HC425D010-HM40525830-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580129
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC425D010-HM40525830-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2073.9 lumens
Efficiency: N/A
Efficacy: 77.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580129

CATALOG NUMBER: HC425D010-HM40525830-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P580129

CATALOG NUMBER: HC425D010-HM40525830-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45	45	45	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	206826
5°	207022
10°	207411
15°	210457
20°	205201
25°	192523
30°	170300
35°	129496
40°	81587
45°	46854
50°	24850
55°	10322
60°	2763
65°	2335
70°	1695
75°	1525
80°	1137
85°	2264



TEST NUMBER: P580129

CATALOG NUMBER: HC425D010-HM40525830-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.0	7.7
10°-20°	461.5	22.3
20°-30°	644.0	31.1
30°-40°	530.0	25.6
40°-50°	218.3	10.5
50°-60°	49.2	2.4
60°-70°	7.9	0.4
70°-80°	2.9	0.1
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1264.5	61.0
0°-40°	1794.5	86.5
0°-60°	2062.0	99.4
0°-90°	2073.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2073.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1677	
5°	1672	159
15°	1648	461
25°	1415	644
35°	860	530
45°	269	218
55°	48	49
65°	8	8
75°	3	3
85°	2	1
90°	0	



TEST NUMBER: P580129

CATALOG NUMBER: HC425D010-HM40525830-41WDBB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1676.8
2.5°	1668.9
5°	1672.0
7.5°	1665.6
10°	1656.0
12.5°	1651.3
15°	1648.1
17.5°	1619.3
20°	1563.3
22.5°	1493.0
25°	1414.6
27.5°	1320.4
30°	1195.7
32.5°	1042.2
35°	860.0
37.5°	676.2
40°	506.7
42.5°	369.3
45°	268.6
47.5°	191.8
50°	129.5
52.5°	81.5
55°	48.0
57.5°	23.9
60°	11.2
62.5°	9.6
65°	8.0
67.5°	6.4
70°	4.7
72.5°	3.2
75°	3.2
77.5°	1.6
80°	1.6
82.5°	1.6
85°	1.6
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)