

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580439

Luminaire Tested: **HC435D010-HM43040835-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580439
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC435D010-HM43040835-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3764.0 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580439

CATALOG NUMBER: HC435D010-HM43040835-41WDH

Luminous Intensity Polar Plot





TEST NUMBER: P580439

CATALOG NUMBER: HC435D010-HM43040835-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	316456
5°	318828
10°	322803
15°	330926
20°	333365
25°	323815
30°	296904
35°	244296
40°	178068
45°	115582
50°	65166
55°	30945
60°	12236
65°	7588
70°	5121
75°	3384
80°	1705
85°	3397



TEST NUMBER: P580439

CATALOG NUMBER: HC435D010-HM43040835-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.9	6.5
10°-20°	730.6	19.4
20°-30°	1083.7	28.8
30°-40°	1000.9	26.6
40°-50°	522.6	13.9
50°-60°	143.3	3.8
60°-70°	27.6	0.7
70°-80°	7.8	0.2
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2060.1	54.7
0°-40°	3061.1	81.3
0°-60°	3727.0	99.0
0°-90°	3764.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3764.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2566	
5°	2575	246
15°	2592	731
25°	2379	1084
35°	1622	1001
45°	663	523
55°	144	143
65°	26	28
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P580439

CATALOG NUMBER: HC435D010-HM43040835-41WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2565.6
2.5°	2558.6
5°	2575.0
7.5°	2582.1
10°	2577.3
12.5°	2582.1
15°	2591.5
17.5°	2582.1
20°	2539.7
22.5°	2471.2
25°	2379.3
27.5°	2254.3
30°	2084.6
32.5°	1870.0
35°	1622.4
37.5°	1363.0
40°	1105.9
42.5°	870.1
45°	662.6
47.5°	485.8
50°	339.6
52.5°	226.4
55°	143.9
57.5°	84.9
60°	49.6
62.5°	35.4
65°	26.0
67.5°	18.9
70°	14.2
72.5°	9.4
75°	7.1
77.5°	4.7
80°	2.4
82.5°	2.4
85°	2.4
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)