

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580133

Luminaire Tested: **HC425D010-HM40525830-41WDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580133  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC425D010-HM40525830-41WDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2553.7 lumens  
Efficiency: N/A  
Efficacy: 95.3 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580133

CATALOG NUMBER: HC425D010-HM40525830-41WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P580133

CATALOG NUMBER: HC425D010-HM40525830-41WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	214708
5°	216308
10°	219022
15°	224529
20°	226177
25°	219688
30°	201435
35°	165740
40°	120811
45°	78427
50°	44212
55°	20967
60°	8289
65°	5137
70°	3462
75°	2335
80°	1137
85°	2264



TEST NUMBER: P580133

CATALOG NUMBER: HC425D010-HM40525830-41WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	166.8	6.5
10°-20°	495.7	19.4
20°-30°	735.2	28.8
30°-40°	679.1	26.6
40°-50°	354.6	13.9
50°-60°	97.1	3.8
60°-70°	18.7	0.7
70°-80°	5.3	0.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1397.7	54.7
0°-40°	2076.8	81.3
0°-60°	2528.6	99.0
0°-90°	2553.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2553.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1741	
5°	1747	167
15°	1758	496
25°	1614	735
35°	1101	679
45°	450	355
55°	98	97
65°	18	19
75°	5	5
85°	2	1
90°	0	



TEST NUMBER: P580133

CATALOG NUMBER: HC425D010-HM40525830-41WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1740.7
2.5°	1735.8
5°	1747.0
7.5°	1751.9
10°	1748.7
12.5°	1751.9
15°	1758.3
17.5°	1751.9
20°	1723.1
22.5°	1676.7
25°	1614.2
27.5°	1529.5
30°	1414.3
32.5°	1268.7
35°	1100.7
37.5°	924.8
40°	750.3
42.5°	590.4
45°	449.6
47.5°	329.6
50°	230.4
52.5°	153.5
55°	97.5
57.5°	57.6
60°	33.6
62.5°	24.0
65°	17.6
67.5°	12.8
70°	9.6
72.5°	6.4
75°	4.9
77.5°	3.2
80°	1.6
82.5°	1.6
85°	1.6
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)