

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580456

Luminaire Tested: **HC435D010-HM43040840-41NDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580456
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC435D010-HM43040840-41NDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3422.8 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580456

CATALOG NUMBER: HC435D010-HM43040840-41NDH

Luminous Intensity Polar Plot





TEST NUMBER: P580456

CATALOG NUMBER: HC435D010-HM43040840-41NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	63	63	63	63
7	81	72	65	61	80	71	65	61	70	64	60	68	64	60	67	63	60	58	58	58	58
8	77	67	61	57	76	67	61	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48	48	48	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	443921
5°	435872
10°	413433
15°	386564
20°	351086
25°	310668
30°	258420
35°	186339
40°	116302
45°	67071
50°	37860
55°	18042
60°	10336
65°	7909
70°	5337
75°	3527
80°	3481
85°	3538



TEST NUMBER: P580456

CATALOG NUMBER: HC435D010-HM43040840-41NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.0	9.6
10°-20°	844.5	24.7
20°-30°	1038.6	30.3
30°-40°	771.4	22.5
40°-50°	313.6	9.2
50°-60°	86.8	2.5
60°-70°	27.0	0.8
70°-80°	9.1	0.3
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2212.1	64.6
0°-40°	2983.5	87.2
0°-60°	3383.9	98.9
0°-90°	3422.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3422.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3599	
5°	3520	329
15°	3027	844
25°	2283	1039
35°	1238	771
45°	384	314
55°	84	87
65°	27	27
75°	7	9
85°	2	3
90°	0	



TEST NUMBER: P580456

CATALOG NUMBER: HC435D010-HM43040840-41NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3599.0
2.5°	3564.5
5°	3520.3
7.5°	3431.5
10°	3300.9
12.5°	3165.2
15°	3027.2
17.5°	2862.0
20°	2674.7
22.5°	2484.8
25°	2282.7
27.5°	2063.3
30°	1814.4
32.5°	1530.9
35°	1237.5
37.5°	961.4
40°	722.3
42.5°	527.5
45°	384.5
47.5°	276.1
50°	197.3
52.5°	135.6
55°	83.9
57.5°	54.2
60°	41.9
62.5°	34.5
65°	27.1
67.5°	19.7
70°	14.8
72.5°	12.4
75°	7.4
77.5°	4.9
80°	4.9
82.5°	2.5
85°	2.5
87.5°	2.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)