

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580168

Luminaire Tested: **HC425D010-HM40525840-41NDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580168
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC425D010-HM40525840-41NDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2364.1 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580168

CATALOG NUMBER: HC425D010-HM40525840-41NDH

Luminous Intensity Polar Plot





TEST NUMBER: P580168

CATALOG NUMBER: HC425D010-HM40525840-41NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 96 | 95 | 93 | 93 | 93 | 93 |
| 2 | 107 | 102 | 98 | 94 | 105 | 100 | 96 | 93 | 97 | 94 | 91 | 94 | 91 | 89 | 91 | 89 | 87 | 86 | 86 | 86 | 86 |
| 3 | 101 | 95 | 89 | 85 | 99 | 93 | 88 | 84 | 91 | 86 | 83 | 88 | 85 | 82 | 86 | 83 | 81 | 79 | 79 | 79 | 79 |
| 4 | 96 | 88 | 82 | 78 | 94 | 87 | 81 | 77 | 85 | 80 | 76 | 82 | 79 | 75 | 81 | 77 | 74 | 73 | 73 | 73 | 73 |
| 5 | 91 | 82 | 76 | 71 | 89 | 81 | 75 | 71 | 79 | 74 | 70 | 77 | 73 | 70 | 76 | 72 | 69 | 67 | 67 | 67 | 67 |
| 6 | 86 | 76 | 70 | 66 | 84 | 76 | 70 | 65 | 74 | 69 | 65 | 73 | 68 | 64 | 71 | 67 | 64 | 63 | 63 | 63 | 63 |
| 7 | 81 | 72 | 65 | 61 | 80 | 71 | 65 | 61 | 70 | 64 | 60 | 68 | 64 | 60 | 67 | 63 | 60 | 58 | 58 | 58 | 58 |
| 8 | 77 | 67 | 61 | 57 | 76 | 67 | 61 | 56 | 65 | 60 | 56 | 64 | 59 | 56 | 63 | 59 | 56 | 54 | 54 | 54 | 54 |
| 9 | 73 | 63 | 57 | 53 | 72 | 63 | 57 | 53 | 62 | 56 | 52 | 61 | 56 | 52 | 60 | 55 | 52 | 51 | 51 | 51 | 51 |
| 10 | 70 | 59 | 53 | 49 | 69 | 59 | 53 | 49 | 58 | 53 | 49 | 57 | 52 | 49 | 57 | 52 | 49 | 48 | 48 | 48 | 48 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 306625 |
| 5° | 301048 |
| 10° | 285554 |
| 15° | 267001 |
| 20° | 242493 |
| 25° | 214570 |
| 30° | 178490 |
| 35° | 128713 |
| 40° | 80331 |
| 45° | 46348 |
| 50° | 26155 |
| 55° | 12451 |
| 60° | 7129 |
| 65° | 5458 |
| 70° | 3679 |
| 75° | 2431 |
| 80° | 2415 |
| 85° | 2406 |



TEST NUMBER: P580168

CATALOG NUMBER: HC425D010-HM40525840-41NDH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 227.3 | 9.6 |
| 10°-20° | 583.3 | 24.7 |
| 20°-30° | 717.4 | 30.3 |
| 30°-40° | 532.8 | 22.5 |
| 40°-50° | 216.6 | 9.2 |
| 50°-60° | 60.0 | 2.5 |
| 60°-70° | 18.7 | 0.8 |
| 70°-80° | 6.3 | 0.3 |
| 80°-90° | 1.9 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1527.9 | 64.6 |
| 0°-40° | 2060.7 | 87.2 |
| 0°-60° | 2337.3 | 98.9 |
| 0°-90° | 2364.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2364.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2486 | |
| 5° | 2431 | 227 |
| 15° | 2091 | 583 |
| 25° | 1577 | 717 |
| 35° | 855 | 533 |
| 45° | 266 | 217 |
| 55° | 58 | 60 |
| 65° | 19 | 19 |
| 75° | 5 | 6 |
| 85° | 2 | 2 |
| 90° | 0 | |



TEST NUMBER: P580168

CATALOG NUMBER: HC425D010-HM40525840-41NDH

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 2485.9 |
| 2.5° | 2462.1 |
| 5° | 2431.4 |
| 7.5° | 2370.1 |
| 10° | 2279.9 |
| 12.5° | 2186.2 |
| 15° | 2090.9 |
| 17.5° | 1976.8 |
| 20° | 1847.4 |
| 22.5° | 1716.3 |
| 25° | 1576.6 |
| 27.5° | 1425.1 |
| 30° | 1253.2 |
| 32.5° | 1057.3 |
| 35° | 854.8 |
| 37.5° | 664.1 |
| 40° | 498.9 |
| 42.5° | 364.3 |
| 45° | 265.7 |
| 47.5° | 190.7 |
| 50° | 136.3 |
| 52.5° | 93.6 |
| 55° | 57.9 |
| 57.5° | 37.5 |
| 60° | 28.9 |
| 62.5° | 23.8 |
| 65° | 18.7 |
| 67.5° | 13.7 |
| 70° | 10.2 |
| 72.5° | 8.5 |
| 75° | 5.1 |
| 77.5° | 3.4 |
| 80° | 3.4 |
| 82.5° | 1.7 |
| 85° | 1.7 |
| 87.5° | 1.7 |
| 90° | 0.0 |



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)