

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592699

Luminaire Tested: **HC425D010-HM40525850-41NDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592699
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC425D010-HM40525850-41NDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2520.8 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592699

CATALOG NUMBER: HC425D010-HM40525850-41NDC

Luminous Intensity Polar Plot





TEST NUMBER: P592699

CATALOG NUMBER: HC425D010-HM40525850-41NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94	94	94	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87	87	87	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81	81	81	81
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76	76	76	76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71	71	71	71
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62	62	62	62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58	58	58	58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55	55	55	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	371283
5°	370807
10°	363584
15°	338077
20°	290745
25°	233569
30°	182350
35°	127674
40°	65518
45°	33265
50°	16656
55°	6215
60°	2516
65°	1985
70°	1226
75°	810
80°	1208
85°	0



TEST NUMBER: P592699

CATALOG NUMBER: HC425D010-HM40525850-41NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.1	11.2
10°-20°	730.8	29.0
20°-30°	787.3	31.2
30°-40°	517.3	20.5
40°-50°	160.8	6.4
50°-60°	31.6	1.3
60°-70°	6.7	0.3
70°-80°	2.5	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1801.2	71.5
0°-40°	2318.5	92.0
0°-60°	2510.9	99.6
0°-90°	2520.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2520.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3010	
5°	2995	283
15°	2648	731
25°	1716	787
35°	848	517
45°	191	161
55°	29	32
65°	7	7
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P592699

CATALOG NUMBER: HC425D010-HM40525850-41NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3010.1
2.5°	2994.8
5°	2994.8
7.5°	2971.0
10°	2902.9
12.5°	2793.9
15°	2647.5
17.5°	2451.6
20°	2215.0
22.5°	1959.6
25°	1716.2
27.5°	1489.7
30°	1280.3
32.5°	1082.8
35°	847.9
37.5°	590.8
40°	406.9
42.5°	280.9
45°	190.7
47.5°	129.4
50°	86.8
52.5°	54.5
55°	28.9
57.5°	12.0
60°	10.2
62.5°	8.5
65°	6.8
67.5°	5.1
70°	3.4
72.5°	3.4
75°	1.7
77.5°	1.7
80°	1.7
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)