

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592769

Luminaire Tested: **HC4R35D010-HM43040850-42RMDC**

Issue Date: 9/23/2021

Test Information

Test Method: LM-41-14
Report Number: P592769
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/23/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC4R35D010-HM43040850-42RMDC
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3824.7 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592769

CATALOG NUMBER: HC4R35D010-HM43040850-42RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P592769

CATALOG NUMBER: HC4R35D010-HM43040850-42RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86		
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80		
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74		
5	92	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69		
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64		
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60		
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56		
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52		
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	433412
5°	442695
10°	460175
15°	460360
20°	425629
25°	367802
30°	299225
35°	219798
40°	127042
45°	59343
50°	27441
55°	9548
60°	3059
65°	2160
70°	1767
75°	1191
80°	0
85°	0



TEST NUMBER: P592769

CATALOG NUMBER: HC4R35D010-HM43040850-42RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	344.9	9.0
10°-20°	999.1	26.1
20°-30°	1230.4	32.2
30°-40°	898.3	23.5
40°-50°	292.7	7.7
50°-60°	48.9	1.3
60°-70°	7.6	0.2
70°-80°	2.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2574.5	67.3
0°-40°	3472.8	90.8
0°-60°	3814.4	99.7
0°-90°	3824.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3824.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3514	
5°	3575	345
15°	3605	999
25°	2702	1230
35°	1460	898
45°	340	293
55°	44	49
65°	7	8
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P592769

CATALOG NUMBER: HC4R35D010-HM43040850-42RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3513.8
2.5°	3516.3
5°	3575.4
7.5°	3644.6
10°	3674.1
12.5°	3664.2
15°	3605.1
17.5°	3457.1
20°	3242.6
22.5°	2983.7
25°	2702.5
27.5°	2409.2
30°	2100.9
32.5°	1785.2
35°	1459.7
37.5°	1131.9
40°	789.0
42.5°	515.4
45°	340.2
47.5°	224.4
50°	143.0
52.5°	83.9
55°	44.4
57.5°	17.3
60°	12.4
62.5°	9.9
65°	7.4
67.5°	4.9
70°	4.9
72.5°	2.5
75°	2.5
77.5°	2.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)